



Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Contacts



Contact Type: **Pin**

Connector System: **Wire-to-Board**

Contact Mating Area Plating Material: **Gold**

Packaging Method: **Loose Piece**

Connector & Contact Terminates To: **Printed Circuit Board**

Features

Product Type Features

Connector System	Wire-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Contact Features

Mating Square Post Dimension	.64 mm[.025 in]
	15 µin
Contact Shape & Form	Square
Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Gold
Contact Base Material	Phosphor Bronze
Contact Type	Pin
Contact Mating Area Plating Material	Gold

Termination Features

Square Termination Post & Tail Dimension	.64 mm[.025 in]
--	-----------------

Mechanical Attachment

Wire Insulation Support	With
Connector Mounting Type	Board Mount

Operation/Application

Circuit Application	Signal
---------------------	--------



Packaging Features

Packaging Quantity	1000
Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




Also in the Series | AMPMODU IV/V



Automotive Headers(2)



Automotive Housings(4)



Backplane Connector Housings(1)



Board-to-Board Connector Contacts(6)



Board-to-Board Headers & Receptacles(937)



Insertion & Extraction Tools(4)



PCB Connector Covers(18)



PCB Connector Keying(6)



PCB Connector Mounting(1)



PCB Connector Strain Relief(3)



PCB Latches, Locks & Retainers(9)



Rectangular Connector Housings(5)



Standard Rectangular Connectors(8)



Wire-to-Board Connector Assemblies & Housings(472)



Wire-to-Board Connector Contacts (328)

Customers Also Bought



TE Part #103653-7
08 MTE SHRD PIN HSG SR LATCH



TE Part #2-2176378-1
RQ 0805 16R2 0.1% 10PPM 5K RL



TE Part #2-535512-9
58 MODII HORZ DR CE EESS .100



TE Part #2-1617352-0
SMGAD-12=SMGAD .100 GRID SMD D



TE Part #2214593-1
zQSF+ STACKED RECEPTACLE
ASSEMBLY 2X2

TE Part #1617124-1
JMAPD-12XP = M39016/15-037P

TE Part #2007850-3
IMP100S,H,V5P10C,UG,DEW46,5.5

TE Part #2007884-2
IMP100S,H,V6P10C,UG,OEWS39,4.9

TE Part #3-1617542-2
JMAPD-12XM=M39016/15-037M

TE Part #ZPF000000000139669
M39029/64-369

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_85891-3_AZ.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_85891-3_AZ.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_85891-3_AZ.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

AMPMODU Mod I And II Posts

English

Application Specification

Japanese

AMPMODU Mod I And II Posts

Japanese