




Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > FFC Contacts > 2.54mm FFC Connectors Socket Contacts



Connector System: **Cable-to-Cable**

Centerline (Pitch): **2.54 mm [.1 in]**

Compatible With Wire & Cable Type: **Discrete Wire**

Contact Type: **Socket**

Contact Mating Area Plating Material: **Gold Flash/Palladium Nickel or Gold/Nickel**

[All 2.54mm FFC Connectors Socket Contacts \(35\)](#)

Features

Product Type Features

Connector System	Cable-to-Cable
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Contact Features

	15 µin
Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Gold Flash
Contact Base Material	Phosphor Bronze
Contact Type	Socket
Contact Mating Area Plating Material	Gold Flash/Palladium Nickel or Gold/Nickel
Contact Current Rating (Max)	2 A



Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Housing Features

Centerline (Pitch)	2.54 mm[.1 in]
--------------------	----------------

Dimensions

Accepts Conductor Width	1.27 mm, 1.82 mm
Wire Size	.12 – .4 mm ²
Accepts Wire Insulation Diameter Range	1.02 – 1.42 mm[.04 – .056 in]

Usage Conditions

Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Packaging Features

Packaging Method	Box
------------------	-----

Other

Comment	Use Extraction Tool No. 91092-1 for end locking slot and Extraction Tool No. 91093-1 for side locking lance slot.
---------	---

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-F439-R2435254
2.54mm FFC Connectors Receptacle Housing

TE Part # 58535-1
PRO-CRIMPER ASSY MODU MODII

TE Part # 58535-2
PRO-CRIMPER ASSY MODU

TE Part # 91537-1
CCII .100 FFC PIN REC 26-22 ASSY

TE Part # 91537-3
CCII .100 FFC PIN REC 26-22 HEAD

Customers Also Bought

TE Part #1-88859-0
2.54mm FFC Connectors Receptacle Housing

TE Part #86561-4
2.54mm FFC Connectors Pin Contacts

TE Part #1623096-1
CRG0805 1% 100R

TE Part #1-770254-0
UMNII GROUND PIN LP DUPL BR



TE Part #130102
TERMINAL PLAS-GRP RNG-TNG 5MM




TE Part #1623117-1
CRG0805 1% 150R




TE Part #1622397-1
LR1 1% 24K



TE Part #1622595-1
LR1 1% 9K1



TE Part #1-5111595-9
068 ASSY SYS 50 PADDLEBOARD



TE Part #1337769-5
50 OHM COAX BNC STR PLUG P99-E

Documents

Product Drawings

RND WIRE RCPT L.P.

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_86571-2_E.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_86571-2_E.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_86571-2_E.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English



Extraction Tools

English

Instruction Sheet (U.S.)

English

Extraction Tool for Flexible Flat Cable (FFC)

English