




Connectors > PCB Connectors > PCB Connector Accessories > PCB Connector Hardware > PCB Latches, Locks & Retainers



Connector & Contact Retention Accessory Type: Locking Device

Contact Current Rating (Max): 3 A

Circuit Application: Signal

Operating Temperature Range: -65 – 105 °C [-85 – 221 °F]

Features

Product Type Features

Connector & Contact Retention Accessory Type	Locking Device
--	----------------

Body Features

Primary Product Material	Polyamide 6.6 GF
Primary Product Color	Red

Contact Features

Contact Current Rating (Max)	3 A
------------------------------	-----

Usage Conditions

Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

Glow Wire Rating	Standard Part - Not Glow Wire
------------------	-------------------------------

Packaging Features

Packaging Quantity	2000
Packaging Method	Box

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUL 2017 (174) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles'(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts




Also in the Series | [AMPMODU IV/V](#)



Automotive Headers(2)



Automotive Housings(4)



Backplane Connector Housings(1)




Board-to-Board Connector Contacts(6)



Board-to-Board Headers & Receptacles(937)



Insertion & Extraction Tools(4)



PCB Connector Covers(18)



PCB Connector Keying(6)



PCB Connector Mounting(1)



PCB Connector Strain Relief(3)



PCB Latches, Locks & Retainers(9)



Rectangular Connector Housings(5)



Standard Rectangular Connectors(8)



Wire-to-Board Connector Assemblies & Housings(472)



Wire-to-Board Connector Contacts (328)

Customers Also Bought



TE Part #1-929504-6
TIMER, CONNECTOR HOUSING



TE Part #1-1633919-6
ANVIL COMBINATION



TE Part #2151266-1
OCEAN-2.0-APPLICATOR-S-070F080BX



TE Part #2836860-2
OCEAN_2.0_APPLICATOR-S-110F180F






ANVIL REPRESENTATION ONLY

TE Part #3-1633932-1
[ANVIL, COMBINATION](#)




CRIMPER REPRESENTATION ONLY

TE Part #4-1803019-0
[CRIMPER, INSULATION O](#)



TE Part #46322-2
[HYP8 AMPPOWER 1/0AWG 69065 DIE SET](#)



TE Part #46323-2
[HYP8 AMPPOWER 2/0AWG 69065 DIE SET](#)



TE Part #CT69303001
[ACW0219-1.00-90\(NS\)](#)



TE Part #364306-000
[RMW-75/22-1000/ADH-0](#)

Documents

Product Drawings

[LOCKING SLIDE](#)

English

CAD Files

[3D PDF](#)

English

Customer View Model

[ENG_CVM_926635-2_D.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_926635-2_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_926635-2_D.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Product Specification](#)

English