



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (.3% in BODY & NUT) Cd (3% in BODY & NUT) Article Safe Usage Statements: Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #205841-1
CPC RECPT ASSEMBLY SIZE 11-8

TE Part #1-640518-0
03P MR II PLUG HSG V0 RED

TE Part #1623141-1
CRG0805 1% 1M0

TE Part #1-640520-0
06P MR II PLUG HSG V0 RED

TE Part #1623133-1
CRG0805 1% 1K2

TE Part #1622531-1
LR1 1% 5K6

TE Part #1676363-1
RN 0805 4K99 0.1% 10PPM CUT LENGTH

TE Part #1622304-1
LR1 1% 110R

TE Part #2-1904045-4
V23333Z0002A041-EV-100

TE Part #ZPF000000000167407
983-6RS 10-05 SY

Documents

Product Drawings
BNX40AB00-1612AX

English

CAD Files
3D PDF

3D

Customer View Model
ENG_CVM_CVM_C49110-000_O.2d_dxf.zip

English

Customer View Model
ENG_CVM_CVM_C49110-000_O.3d_igs.zip

English

Customer View Model
ENG_CVM_CVM_C49110-000_O.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages



5-1654025-5_sec6_Adapters

English

Circular Backshells

English

Product Specifications

General Information Package for BNDXXA (Band Strap) Adapters

English

Instruction Sheets

Instruction Sheet (U.S.)

English