1394871-1 ✔ ACTIVE

AMP | MQS

TE Internal #: 1394871-1

MQS, Automotive Seals & Cavity Plugs, PA GF, Black

View on TE.com >

Connectors > Automotive Connectors > Seals & Cavity Plugs



Seal Material: **PA GF**

Contains Lubricant: **No**

Primary Product Color: **Black**

Features

Body Features

Seal Material	PA GF
Primary Product Color	Black

Packaging Features

Packaging Quantity	10048
Packaging Method	Bag

Other

Contains Lubricant	No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # CAT-M8793-CH8172
MQS, CONNECTOR HOUSING



TE Part # CAT-T4827-CH8172
TIMER, CONNECTOR HOUSING



TE Part # 2209544-9
60P,PLUG ASSY,NORMAL CODING



TE Part # 2209545-1
94P,MQS CB,REC HSG,ASSY,SEALED



TE Part # 2050036-4
64P ECU PLUG CONNECTOR



TE Part # 2050036-1
64P ECU PLUG CONNECTOR



TE Part # 2050036-5
64P ECU PLUG CONNECTOR



TE Part # 2137491-1
48 POS MIXED REC HSG GREY W/ C



TE Part # 2209544-1
60P,MQS CB,REC HSG,ASSY,SEALED



TE Part # 2299987-1
65W PLUG ASSEMBLY



TE Part # 2299987-3
65W PLUG ASSEMBLY



TE Part # 2299987-4
65W PLUG ASSEMBLY

TE Part # 3-2289228-1
CONNECTOR, 94POS

TE Part # 7-2289227-1
CONNECTOR, 60POS

TE Part # 7-2289228-1
CONNECTOR, 94POS

TE Part # 9-2289227-1
CONNECTOR, 60POS

TE Part # 9-2289228-1
CONNECTOR, 94POS


Also in the Series | MQS



Automotive Connector Caps & Covers (133)



Automotive Connector EMC Shielding (2)



Automotive Connector Locks & Position Assurance(29)



Automotive Headers(207)



Automotive Housings(498)



Automotive Seals & Cavity Plugs(26)



Automotive Terminals(98)



Data Connectivity Headers(1)



Insertion & Extraction Tools(42)



Other Automotive Connector Accessories(13)


Customers Also Bought




TE Part #1241414-1
AMP MCP, RECEPTACLE AND TAB



TE Part #1-1355133-1
HEBEL F.AUFNAHM-GEH



TE Part #1-1355118-1
RETAINER FOR 60POS SOCKET HSG




TE Part #1-1355135-1
RETAINER 94P



TE Part #1-1355134-1
RETAINER 94P



TE Part #1-1452424-2
BLIND PLUG FOR MCON 1.2 CB (1.



TE Part #968221-1
MQS0,63 Sn rec CB unseal. 0,5-0,75

Documents

Product Drawings

MQS DICHTSTOPFEN

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1394871-1_A_c-1394871-1-a.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1394871-1_A_c-1394871-1-a.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1394871-1_A_c-1394871-1-a.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

Application Specification

English

Product Environmental Compliance

Product Compliance

English

Product Compliance

English