TE Internal #: 1408496-1

RF Connectors, MMCX RF Interface, Plug, RF Connector Mated

Outer Diameter (Approximate) .106 in [2.7 mm], 50 Ω , Push-On,

6GHz Operating Frequency

View on TE.com >



Connectors > RF Coax Connectors > RF Connectors > MMCX Connector: Male (Jack)











RF Interface: MMCX

RF Connector Style: Plug

RF Connector Mated Outer Diameter (Approximate): 2.7 mm [.106 in]

Impedance: 50Ω

RF Connector Coupling Mechanism: Push-On

All MMCX Connector: Male (Jack) (10)

Features

Product Type Features

RF Interface	MMCX
RF Connector Style	Plug
Connector System	Cable-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	1
PCB Mount Orientation	Vertical
Number of Coaxial Contacts	1

Electrical Characteristics

Impedance	50 Ω	

Body Features

Body Material Brass



Body Plating Material	Gold
Contact Features	
RF Connector Center Contact Underplating Material	Nickel
RF Connector Center Contact Plating Material	Gold
RF Connector Center Contact Material	Brass
Termination Features	
Termination Method to Printed Circuit Board	Surface Mount
Termination Post & Tail Length	3 mm[.118 in]
Mechanical Attachment	
RF Connector Coupling Mechanism	Push-On
Connector Mounting Type	Panel Mount
RF Contact Captivation Method	Mechanical
Detent	Without
Dimensions	
RF Connector Mated Outer Diameter (Approximate)	2.7 mm[.106 in]
Height Above PC Board	4.5 mm[.177 in]
Usage Conditions	
Operating Temperature Range	-65 – 165 °C[-85 – 329 °F]
Operation/Application	
Operating Frequency	6 GHz
Packaging Features	
Packaging Method	Bag
Other	
Dielectric Material	PTFE

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211)



Candidate List Declared Against: JAN 2021 (211)

SVHC > Threshold:

Pb (3.7% in Component Part)

Article Safe Usage Statements:

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Bromine/Chlorine - Br and Cl < 900

ppm per homogenous material. Also BFR

/CFR/PVC Free

Solder Process Capability

Pin-in-Paste capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts









Customers Also Bought





















Documents

Product Drawings

MMCX STRAIGHT PCB PLUG

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1408496-1_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1408496-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1408496-1_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Datasheets & Catalog Pages

MCX Connectors

English

Product Specifications

Product Specification

English

Product Environmental Compliance

TE Material Declaration

RF Connectors, MMCX RF Interface, Plug, RF Connector Mated Outer Diameter (Approximate) .106 in [2.7 mm], 50 Ω , Push-On, 6GHz Operating Frequency



English