



Connectors > Automotive Connectors > Connector Accessories > Other Connector Accessories > DEUTSCH DT MOUNTING CLIPS



Automotive Connector Accessory Type: **Mounting Clip**  
Connector System: **Wire-to-Wire**  
Primary Product Material: **Stainless Steel**  
Connector & Contact Terminates To: **Wire & Cable**  
Operating Temperature Range: **-55 – 125 °C [ -67 – 257 °F ]**

[All DEUTSCH DT MOUNTING CLIPS \(10\)](#)

Features

Product Type Features

|                                     |               |
|-------------------------------------|---------------|
| Automotive Connector Accessory Type | Mounting Clip |
| Connector System                    | Wire-to-Wire  |
| Connector & Contact Terminates To   | Wire & Cable  |

Body Features

|                          |                 |
|--------------------------|-----------------|
| Primary Product Material | Stainless Steel |
|--------------------------|-----------------|

Usage Conditions

|                             |                            |
|-----------------------------|----------------------------|
| Operating Temperature Range | -55 – 125 °C[-67 – 257 °F] |
|-----------------------------|----------------------------|

Packaging Features

|                    |      |
|--------------------|------|
| Packaging Quantity | 1000 |
| Packaging Method   | Box  |

Other

|             |     |
|-------------|-----|
| Serviceable | Yes |
|-------------|-----|

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

|                              |           |
|------------------------------|-----------|
| EU RoHS Directive 2011/65/EU | Compliant |
|------------------------------|-----------|



|                                               |                                                                                                                               |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                     |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                       |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2021 (211)<br>Candidate List Declared Against: JAN 2021 (211)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                           |
| Solder Process Capability                     | Not reviewed for solder process capability                                                                                    |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

|                                                                                                                                                                      |                                                                                                                                                              |                                                                                                                                                                |                                                                                                                                                            |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------|
|  <p>TE Part # CAT-D487-CH8172<br/>DEUTSCH DT Series Housings &amp; Connectors</p> |  <p>TE Part # CAT-D485-CH8172<br/>DEUTSCH DTM HOUSINGS</p>                |  <p>TE Part # CAT-D48-PCH8172<br/>DEUTSCH DTHD HOUSINGS</p>               |  <p>TE Part # CAT-D486-CH8172<br/>DEUTSCH DTP HOUSINGS</p>            |
|  <p>TE Part # 1-2350890-2<br/>20POS, HYBRID, SOC HSG ASSY, SLD, COD B</p>         |  <p>TE Part # 1-2350890-3<br/>20POS, HYBRID, SOC HSG ASSY, SLD, COD C</p> |  <p>TE Part # 1-2350890-4<br/>20POS, HYBRID, SOC HSG ASSY, SLD, COD D</p> |  <p>TE Part # 2318967-1<br/>24POS, AMP MCP 2.8, REC HSG ASSY, SLD</p> |




|  |  |  |  |
|--|--|--|--|
|  |  |  |  |
|  |  |  |  |
|  |  |  |  |

Also in the Series | DEUTSCH DT

|  |  |  |  |
|--|--|--|--|
|  |  |  |  |
|  |  |  |  |

Customers Also Bought





Documents

Product Drawings  
CLIP, SS, 11MM HOLE, ST  
English

CAD Files  
3D PDF  
3D  
Customer View Model  
ENG\_CVM\_CVM\_1027-003-1200\_99\_c-1027-003-1200-99.2d\_dxf.zip  
English  
Customer View Model  
ENG\_CVM\_CVM\_1027-003-1200\_99\_c-1027-003-1200-99.3d\_igs.zip  
English  
Customer View Model  
ENG\_CVM\_CVM\_1027-003-1200\_99\_c-1027-003-1200-99.3d\_stp.zip  
English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages  
CONNECTOR SELECTOR  
English

Product Specifications  
Application Specification  
English

Instruction Sheets  
Instruction Sheet (U.S.)



English