



Connectors > Power Connectors > Power Contacts



Power Contact Type: **Contact**

Contact Mating Area Plating Material: **Gold**

Wire Size: **24 – 20 AWG**

Connector System: **Wire-to-Wire**

Connector & Contact Terminates To: **Wire & Cable**

Features

Product Type Features

Power Contact Type	Contact
Connector System	Wire-to-Wire
Connector & Contact Terminates To	Wire & Cable

Contact Features

Contact Mating Area Plating Material	Gold
Contact Current Rating (Max)	5 A
Contact Type	Pin
Contact Retention Within Housing	Without
Mating Pin Diameter	1.02 mm[.04 in]
Contact Base Material	Copper
Contact Mating Area Plating Material Thickness	.25 µm[10 µin]
Wire Contact Termination Area Plating Material Thickness	.25 µm[10 µin]
Wire Contact Termination Area Plating Material	Gold
Contact Orientation	Straight



Contact Underplating Material	Nickel
Contact Underplating Material Thickness	1.27 µm[50 µin]
Contact Size	20

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
Wire Insulation Support	Without

Dimensions

Wire Size	24 – 20 AWG
-----------	-------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

Glow Wire Rating	Standard Part - Not Glow Wire
------------------	-------------------------------

Packaging Features

Packaging Method	Bag
Packaging Quantity	2000

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Pb (3.7% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC



Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1643917-1
703-14-00100

TE Part # 601967-2
POSITIONER M22520/1-02

Also in the Series | ELCON Drawer

PCB Connector Mounting(1)

Power Contacts(37)

Rectangular Power Connectors(35)

Customers Also Bought


TE Part #1648183-1
291-10-01100=SA CONN,PIN

TE Part #1648110-1
221-0010-01100=SA CONN,PIN


TE Part #1648203-1
297-08-01100=SA CONN,PIN

TE Part #1643906-1
Crown Clip Senior 538-17-00100 399-01 7





TE Part #87809-1
MOD V RECP PLTD 30 AU



TE Part #1643915-1
703-12-00100



TE Part #1648157-1
242-28-01100



TE Part #1648151-1
241-27-01100



TE Part #1648162-1
261-0006-01100

TE Part #1643784-1
291-0171-00100B=TA CONN,PIN

Documents

Product Drawings

701-14-02109=CONTACT,PIN,#20

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1650155-1_Y.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1650155-1_Y.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1650155-1_Y.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

POWER_CONNECTORS_CATALOG_SEC02_CABLE_MOUNTED

English

AMP & ELCON Power Connector Layout Forms Datasheet 6-1773444-7

English

Product Specifications

Application Specification

English



Product Environmental Compliance

[MD_1650155-1_08162018446_dmtec](#)

English

[MD_1650155-1_08162018446_dmtec](#)

English