



Connectors > Automotive Connectors > Seals & Cavity Plugs



Connector Seal Type: **Single Wire Seal (SWS)**
Cavity Diameter: **3.6 mm [.142 in]**
Accepts Cable Insulation Diameter Range: **.9 – 1.2 mm [.035 – .047 in]**
Seal Material: **Silicone**
Resistance to Hydrocarbons: **Poor**

Features

Product Type Features

Connector Seal Type	Single Wire Seal (SWS)
---------------------	------------------------

Body Features

Seal Material	Silicone
Primary Product Color	Green

Dimensions

Cavity Diameter	3.6 mm[.142 in]
Accepts Cable Insulation Diameter Range	.9 – 1.2 mm[.035 – .047 in]

Usage Conditions

Operating Temperature (Max)	65 °C, 70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C, 130 °C [149 °F][158 °F][167 °F][176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F][266 °F]
Operating Temperature Range	-40 – 130 °C[-40 – 266 °F]

Industry Standards

--	--



UL Flammability Rating	None
------------------------	------

Other

Resistance to Hydrocarbons	Poor
Shore A Hardness	50
Contains Lubricant	Yes

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # CAT-AM705-CH8172
AMP MCP, SEALED CONNECTOR
HOUSING



TE Part # CAT-M9194-CH8172
MULTILOCK, CONNECTOR HOUSING




TE Part # CAT-AM705-T273
AMP MCP, RECEPTACLE AND TAB




TE Part # CAT-T4827-CH8172
TIMER, CONNECTOR HOUSING


Also in the Series | Timer Connector System




Automotive Connector Caps & Covers
(11)



Automotive Connector Locks &
Position Assurance(16)




Automotive Headers(79)




Automotive Housings(212)




Automotive Seals & Cavity Plugs(31)




Automotive Terminals(143)




Crimp Terminal Housings(13)



Insertion & Extraction Tools(20)



Other Automotive Connector
Accessories(1)



Quick Disconnects(4)

Customers Also Bought



TE Part #1394512-1
EINZELLEITDICHTG,BL



TE Part #1394132-1
BLINDSTOPFEN F.D3,6



TE Part #1394133-1
SINGLE WIRE SEAL BLUE



TE Part #1-1563759-1
HEAVY DUTY SEALED CONNECTOR
HOUSINGS



TE Part #1-967570-1
MQS, CONNECTOR HOUSING



TE Part #969028-5
TIMER, RECEPTACLE AND TAB



TE Part #1394277-2
CIRCULAR DIN BACKSHELLS

Documents

Product Drawings

SINGLE WIRE SEAL,COLLAR DIA 2,

German

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1718705-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1718705-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1718705-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

HDSCS CAN Bus Y-Connector and 120 Resistor Brochure

English

HDSCS Catalog

English

CONNECTOR SELECTOR

English