



Connectors > Automotive Connectors > Seals & Cavity Plugs



Connector Seal Type: **Single Wire Seal (SWS)**

Cavity Diameter: **8.5 mm [.334 in]**

Accepts Cable Insulation Diameter Range: **4.5 mm [.177 in]**

Seal Material: **Silicone**

Resistance to Hydrocarbons: **Poor**

Features

Product Type Features

Connector Seal Type	Single Wire Seal (SWS)
---------------------	------------------------

Body Features

Seal Material	Silicone
Primary Product Color	Green

Dimensions

Cavity Diameter	8.5 mm[.334 in]
Accepts Cable Insulation Diameter Range	4.5 mm[.177 in]

Usage Conditions

Operating Temperature (Max)	65 °C, 70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C, 130 °C [149 °F][158 °F][167 °F][176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F][266 °F]
Operating Temperature Range	-40 – 130 °C[-40 – 266 °F]

Industry Standards

UL Flammability Rating	None
------------------------	------

Other

Resistance to Hydrocarbons	Poor
Shore A Hardness	50
Contains Lubricant	Yes



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-AM7-FRB69
SEALED FUSE & RELAY BOXES




TE Part # CAT-L489-CH8172
LEAVYSEAL HOUSINGS



TE Part # CAT-M4595-CH8172
MCON, CONNECTOR HOUSING



TE Part # CAT-AM705-CH8172
AMP MCP, SEALED CONNECTOR HOUSING



TE Part # CAT-AM705-T273
AMP MCP, RECEPTACLE AND TAB




TE Part # CAT-AM705-CH8173
AMP MCP, UNSEALED CONNECTOR HOUSING




TE Part # CAT-H3399-CH8172
HEAVY DUTY SEALED CONNECTOR HOUSINGS



TE Part # 1-2321910-1
HVA630 3P PLUG ASSY, UNSHIELD



TE Part # 2-1564536-1
4POS,TAB5.8X0.8,TABHSG,ASSY, COD. B



TE Part # 2310318-7
90POS,HYBRID,REC HSG ASSY,SLD, COD A



TE Part # 2310318-8
90POS,HYBRID,REC HSG ASSY,SLD, COD A



TE Part # 2310318-9
90POS,HYBRID,REC HSG ASSY,SLD, COD A



TE Part # 2310319-7
90POS,HYBRID,REC HSG ASSY,SLD, COD A




TE Part # 2310319-8
90POS,HYBRID,REC HSG ASSY,SLD, COD A




TE Part # 2310319-9
90POS,HYBRID,REC HSG ASSY,SLD, COD A



TE Part # 2321910-1
HVA630 3P PLUG ASSY, UNSHIELD



TE Part # 1-2310318-0
90POS,HYBRID,REC HSG ASSY,SLD, COD A



TE Part # 1-2310318-1
90POS,HYBRID,REC HSG ASSY,SLD, COD A



TE Part # 1-2310319-0
90POS,HYBRID,REC HSG ASSY,SLD, COD A




TE Part # 1-2310319-1
90POS,HYBRID,REC HSG ASSY,SLD, COD A

Also in the Series | Timer Connector System



Automotive Connector Caps & Covers (11)



Automotive Connector Locks & Position Assurance(16)



Automotive Headers(79)



Automotive Housings(212)



Automotive Seals & Cavity Plugs(31)



Automotive Terminals(143)



Crimp Terminal Housings(13)



Insertion & Extraction Tools(20)




Other Automotive Connector Accessories(1)



Quick Disconnects(4)

Customers Also Bought



TE Part #967652-1
PQ BLINDSTOPFEN 8,5



TE Part #1-1564544-1
HEAVY DUTY SEALED CONNECTOR HOUSINGS



TE Part #1-962919-1
TIMER, RECEPTACLE AND TAB



TE Part #1241416-3
AMP MCP, RECEPTACLE AND TAB



TE Part #1-1452424-3
BLIND PLUG FOR MCON 1.2 CB (0,75 MM?)

Documents

Product Drawings
SINGLE WIRE SEAL, GREEN

English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_1719043-1_A.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_1719043-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1719043-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[HDSCS Catalog](#)

English

[CONNECTOR SELECTOR](#)

English