




Connectors > Lighting Connectors > Plug & Socket Connectors



Connector System: **Cable-to-Cable**

Number of Positions: **2**

Sealable: **No**

Connector & Contact Terminates To: **Wire & Cable**

Lighting Connector Style: **Plug**

Features

Product Type Features

Product Type	Connector
Wire/Cable Type	Discrete Wire
Connector System	Cable-to-Cable
Sealable	No
Connector & Contact Terminates To	Wire & Cable
Lighting Connector Style	Plug

Configuration Features

Keying Arrangement	HV-1
Number of Positions	2
Contacts Preloaded	No

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Contact Features

Accepts Contact Style	Socket
Contact Type	Socket

Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Housing Features

--	--



Housing Color	Black
---------------	-------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

VDE Tested	Yes
------------	-----

Packaging Features

Packaging Method	Box
------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2018 (181) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts





TE Part # 1740259-1
NECTOR S PLUG HV-1 WHITE



TE Part # 1740336-4
MICRO QUADLOK SYSTEM SOCKET CONTACT



TE Part # 1-293313-0
NECTOR S PCB STRAIGHT OUTLET



TE Part # 293234-9
NECTOR S T SPLITTER HV-1



TE Part # 293313-2
NECTOR S PCB CONN. ASSY STR OUTLET



TE Part # 293315-2
NECTOR S PCB CONN. ASSY 90 DEG OUTLET



TE Part # 293315-7
NECTOR S PCB CONN. ASSY 90 DEG OUTLET



TE Part # 293300-4
NECTOR S BUS BAR ASSY HV-1 BLACK



TE Part # 293300-2
NECTOR S BUS BAR ASSY HV-1 TAB BLACK



TE Part # 1-293270-1
NECTOR S BUS BAR SEALED TAB HV-1 BLACK



TE Part # 1-293270-2
NECTOR S BUS BAR SEALED END CONN, TAB



TE Part # 1-293270-3
NECTOR S BUS BAR SEALED TAB HV-1 BLACK



TE Part # 2-293300-2
NECTOR S BUS BAR ASSY END RUN HV-1 BLACK



TE Part # 293235-6
NECTOR S T SPLITTER SERIAL HV-1 BLACK

Also in the Series | **NECTOR S**



Insertion & Extraction Tools(3)



Lighting Cable Assemblies(1)



Plug & Socket Lighting Connector Accessories(57)



Plug & Socket Lighting Connectors(54)

Customers Also Bought



 TE Part #1658681-1 D-Sub Crimp Recpt Signal 15 Posn, Socket Size 22, Shell Size 1	 TE Part #172165-1 2 CIR UNIV M-N-L PLUG NATL	 TE Part #172168-1 6 CIR UNIV M-N-L PLUG	 TE Part #172160-1 6 CIR UNIV M-N-L CAP
 TE Part #163300-6 MATENLOK SOCKET TP	 TE Part #170360-1 UNIV M-N-L PIN 22-18 AWG	 TE Part #CU7122-000 Thick-Wall Heat Shrink Tubing	 TE Part #1333221-8 ANVIL, EF .130
 TE Part #1740260-2 NECTOR S TUBE BLACK	 TE Part #1740261-2 NECTOR S RING CLIP BLACK		

Documents

Product Drawings
NECTOR S PLUG HV-1 BLACK

English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_1740259-2_E.2d_dxf.zip

English

Customer View Model
ENG_CVM_CVM_1740259-2_E.3d_igs.zip

English

Customer View Model
ENG_CVM_CVM_1740259-2_E.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



NECTOR_S_LINE_CONNECTOR_BROCHURE

English

Product Specifications

Product Specification

English