



Connectors > Rectangular Connectors > Rectangular Connector Accessories > Rectangular Connector Seals



Connector Seal Type: **Interface Seal**
Operating Temperature Range: **-40 – 90 °C [-40 – 194 °F]**

Features

Product Type Features

Product Type	Accessory
Connector Seal Type	Interface Seal

Body Features

Material	Urethane Foam
Seal Material	Urethane Foam

Usage Conditions

Operating Temperature Range	-40 – 90 °C[-40 – 194 °F]
-----------------------------	---------------------------

Operation/Application

For Use With	Mini Universal MATE-N-LOK Sealed Connector
--------------	--

Packaging Features

Packaging Method	Package
Packaging Quantity	1000

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 794942-1
10P MINI UMNL CAP HSG



TE Part # 1-770858-1
10P MINI UMNL HDR ASSY AU LF



TE Part # 794781-1
10P MINI UMNL PLUG HSG




TE Part # 1-770971-1
10P MINI UMNL R/A HDR ASSY LF




TE Part # 1-770858-0
10P MINI UMNL HDR ASSY SNDBL L



TE Part # 794370-1
08P MINI UMNL STR RELIEF HNGD



TE Part # 1-770971-0
10P MINI UMNL R/A HDR ASSY SN



TE Part # 1-1586359-0
10P MINIMUMNL GANG WIRE SEAL DR


Also in the Series | Mini-Universal MATE-N-LOK



Connector Contacts(11)



Insertion & Extraction Tools(1)



Power Contacts(85)



Rectangular Backshells & Clamps(2)



Rectangular Boots & Strain Relief(2)



Rectangular Connector Keying Plugs(2)




Rectangular Connector Locking(1)



Rectangular Connector Seals(18)



Rectangular Power Connectors(285)




Wire-to-Board Headers & Receptacles (1)

Customers Also Bought



TE Part #175152-2
AMP UNIVE. POWER CONN REC CONT



TE Part #1-1586362-6
16P MINI UMNL SEAL,DIE CUT



TE Part #927827-1
TIMER, RECEPTACLE AND TAB



TE Part #1-456405-3
CRIMPER WIRE .080 F



TE Part #1-456405-5
CRIMPER, WIRE .080 "F"



TE Part #151680
2 WAY MATE-N-LOK SOC HSG NAT.



TE Part #1452409-1
2-NDRY F.58P CONNECTOR



TE Part #1586359-4
04P MINIMUMNL GANG WIRE SEAL DR



Documents

Product Drawings

10P MINI UMNL SEAL,DIE CUT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-794772-0_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-794772-0_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-794772-0_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SOFT_SHELL_PIN_SOCKET_CONNECTORS_STANDARD_DENSITY

English

1-1773458-0_MINI_UNIVERSAL_MATE_N_LOK_CONNECTOR_SYSTEM_QRG

English

Product Specifications

Mini-Universal MATE-N-LOK* Splash Proof Seals

English

Product Specification

English

Product Environmental Compliance

Product Compliance

English

Product Compliance

English



Instruction Sheets

Instruction Sheet (U.S.)

English