



Connectors > Rectangular Connectors > Rectangular Contact Inserts

Rectangular Connector Insert Type: **Pin**

Contact Type: **Pin**

Number of Positions: **11**

Features

Product Type Features

Product Type	Contact Module
Rectangular Connector Insert Type	Pin

Configuration Features

Number of Positions	11
---------------------	----

Body Features

Module Material	Phenolic
Color	Black

Contact Features

Contact Type	Pin
--------------	-----

Operation/Application

For Use With	6 Miniature COAXICON Contacts or Type 1 (Size 12) Contacts and 5 Type II (Size 16), Type III+ (Size 16) Type VI (Size 16) or Subminiature COAXICON Contacts.
--------------	--

Packaging Features

Packaging Method	Carton
Packaging Quantity	45

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211)



Candidate List Declared Against: JUN 2020
(209)
SVHC > Threshold:
Not Yet Reviewed

Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 539972-1
EXTRACTION TOOL




TE Part # 305183
EXTRACT TOOL TYPE 2 20-16


Customers Also Bought



TE Part #35278
BUDGET RECT 16-14 8




TE Part #320818
BUDGET RECT 16-14 10




TE Part #66084-3
CONT AMP LEAF L/P 30/3 AU




TE Part #YDTS24F17-06BNV001
D38999: Jam Nut, 17-06 Insert,
Electroless Nickel Plating



TE Part #583631-1
HSG AMP LEAF 30 POS



TE Part #31813
TERMINAL,BUDG RECT 16-14 6



TE Part #66092-1
AMP-LEAF COM SPG 1/16 AU



TE Part #8-146281-6
36 MODII HDR SRST B/A .100CL

TE Part #5-202681-3
RECPT KIT,2 MODULE,G-SERIES



TE Part #4-1393099-3
KA-11DG-12=KA/KB/KC/KR

Documents

Product Drawings
PIN MODULE, 11 POSN, G-SERIES
English

Datasheets & Catalog Pages
Products for Aerospace and Defense
English

Instruction Sheets
Instruction Sheet (U.S.)
English
11-POSITION SERIES "G" MODULES
English

Agency Approvals
Agency Approval Document
English