



Connectors > Rectangular Connectors > Rectangular Contact Inserts



Rectangular Connector Insert Type: **Socket**

Contact Type: **Socket**

Number of Positions: **11**

### Features

#### Product Type Features

Product Type	Contact Module
Rectangular Connector Insert Type	Socket

#### Configuration Features

Number of Positions	11
---------------------	----

#### Body Features

Module Material	Phenolic
Color	Black

#### Contact Features

Contact Type	Socket
--------------	--------

#### Operation/Application

For Use With	(6) Miniature COAXICON or Type I size 12 Socket Contacts and (5) Subminiature COAXICON, Type II Size 16, Type III (+) Size 16 or Type VI Size 16 Socket Contacts
--------------	--

#### Packaging Features

Packaging Method	Carton
Packaging Quantity	45



## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Customers Also Bought


 <p>TE Part #201145-2 COAX MINIATURE SOCKET ASSY</p>	 <p>TE Part #202648-4 PIN MODULE, 11 POSN, G-SERIES</p>	 <p>TE Part #413985-8 SMB Connector: Female (Plug), Mated Outer Dia. 4.75mm, 50 Ohm</p>	 <p>TE Part #31813 TERMINAL,BUDG RECT 16-14 6</p>
---	---	--	--




TE Part #5-120628-8  
LOCKING TRIOMATE ASY 8P(L)LDLFR




TE Part #5225973-1  
PLUG, RT ANGLE, DUAL CRIMP,BNC



TE Part #531477-5  
TWIN LEAF CONTACT LP



TE Part #5767111-9  
MICT,PLG,076,ASY,.025 TAPE CAP



TE Part #767121-9  
MICT,PLG,076,ASY,.025,TAPE PKG



TE Part #5-202832-2  
LOCKING LATCH KIT,G-SERIES

## Documents

### Product Drawings

#### SKT MODULE, 11 POSN, G-SERIES

English

### CAD Files

#### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_202649-4\\_Y.2d\\_dxf.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_202649-4\\_Y.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_202649-4\\_Y.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

#### Products for Aerospace and Defense

English

### Instruction Sheets

#### Instruction Sheet (U.S.)

English

#### 11-POSITION SERIES "G" MODULES

English



[Agency Approvals](#)

[Agency Approval Document](#)

English