



Connectors > Rectangular Connectors > Rectangular Connector Accessories > Locking



Connector & Contact Retention Accessory Type: **TPA (Terminal Position Assurance)**

Operating Temperature Range: **-30 – 105 °C [-22 – 221 °F]**

Features

Product Type Features

Connector & Contact Retention Accessory Type	TPA (Terminal Position Assurance)
--	-----------------------------------

Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

Product Compliance







[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



 TE Part # CAT-G7534-T669 GRACE INERTIA TPA	 TE Part # 2-1971904-6 TPA 12POS,NEW GIC3.3	 TE Part # 2-1971904-2 TPA 4POS,NEW GIC3.3	 TE Part # 2-1971904-4 TPA 8POS,NEW GIC3.3
 TE Part # 2-1971904-5 TPA 10POS,NEW GIC3.3	 TE Part # 2-1971904-7 TPA 14POS,NEW GIC3.3	 TE Part # 4-1971904-2 TPA 4POS,NEW GIC3.3	 TE Part # 4-1971904-3 TPA 6POS,YELLOW,NEW GIC3.3

Also in the Series | GRACE INERTIA 3.3

 PCB Latches, Locks & Retainers(6)	 Power Contacts(1)	 Rectangular Connector Locking(8)	 Rectangular Power Connectors(61)
--	--	---	---

Customers Also Bought



 TE Part #1376395-1 Power Key TPA	 TE Part #170452-2 PL 250 AUTOMOTIVE REC 22-20 AWG PRE TPBR	 TE Part #170213-1 250 FASTON,REC.,18-14 AWG,BR	 TE Part #1-1971905-7 Glow Wire GRACE INERTIA Plug
 TE Part #1376392-2 STD Temp Power Key Plug	 TE Part #1-172210-7 6 POS PL MK-2 187 HOUSING RECEPTACLE	 TE Part #1-1633860-9 CRIMPER, WIRE F	 TE Part #CD26913001 100G1131-0.75-F974CK0042

Documents

Product Drawings
TPA 6POS,NEW GIC3.3

English

CAD Files
3D PDF

3D

Customer View Model
ENG_CVM_CVM_2-1971904-3_C.2d_dxf.zip

English

Customer View Model
ENG_CVM_CVM_2-1971904-3_C.3d_igs.zip

English

Customer View Model
ENG_CVM_CVM_2-1971904-3_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications
Product Specification

English