



Relays, Contactors & Switches > Circuit Breakers



Circuit Breaker Type: **Thermal**

Features

Product Type Features

Product Type	Boot
Circuit Breaker Type	Thermal

Mechanical Attachment

Mounting Bushing	3/8-24 Bushing
------------------	----------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2018 (191) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 4-1423674-9 W54-XB2A99C10-25=CTBKR,THERM,	 TE Part # 2-1393249-8 W58-XB1A6A-20=W58	 TE Part # 5-1423901-9 W54-XB2A4A10-10=CTBKR,THERM, PB,QC.250	 TE Part # 1423901-1 W54-XB2A4A10-5=CTBKR,THERM,PB, QC.250
 TE Part # 2-1423675-3 W57-XB2A99C10-10=CTBKR,THERM,	 TE Part # 2-1423675-0 W57-XB2A99C10-5=CTBKR,THERM,P	 TE Part # 5-1423364-6 W57-XB6A99C10-10=CTBKR,THERM, PB,QC.250	 TE Part # 5-1423364-8 W57-XB6A99C10-12=CTBKR,THERM, PB,QC.250
 TE Part # 5-1423364-7 W57-XB6A99C10-15=CTBKR,THERM, PB,QC.250	 TE Part # 5-1423364-4 W57-XB6A99C10-5=CTBKR,THERM, PB,QC.250	 TE Part # 5-1423364-5 W57-XB6A99C10-7=CTBKR,THERM, PB,QC.250	 TE Part # 2-1423695-4 W58-XB1A6B-15=CTBKR,THERM,PB, QC.250,BUS
 TE Part # 1-1423675-9 W57-XB2A99C10-4=CTBKR,THERM,P	 TE Part # 1423000-7 W54-FA2A6A10-5	 TE Part # 9-1423674-9 W54-XA2C4A10-40=CTBKR,THERM,P	 TE Part # 6-1423901-0 W54-XB2A4A10-15=CTBKR,THERM, PB,QC.250



TE Part # 6-1423901-1
W54-XB2A4A10-20=CKTBKR,THERM,
PB,QC.250

TE Part # 2-1423675-5
W57-XB2A99C10-15=CKTBKR,THERM,
PB,QC.250

TE Part # 2-1423675-6
W57-XB2A99C10-20=CKTBKR,THERM,
PB,QC.250

TE Part # 5-1423364-9
W57-XB6A99C10-20=CKTBKR,THERM,
PB,QC.250

Also in the Series | Potter & Brumfield W57

Circuit Breakers(26)

Customers Also Bought

TE Part #1393249-7
W58-XB1A4A-10=W58

TE Part #1393249-8
W58-XB1A4A-12=W58

TE Part #1-1393249-2
W58-XB1A4A-20=W58

TE Part #1-1393249-9
W58-XB1A4A-5=W58

TE Part #1-1423696-6
BOOTSEAL,M11,CLEAR,SILICONE

TE Part #1-2176091-5
RP 2A 0.25W 80R6 0.1% 25PPM 1K RL

TE Part #1-534237-8
20 MODII VRT SR CE 100/115

TE Part #HD36-18-14PN-059
DEUTSCH HD30 HOUSINGS

TE Part #1393249-6
W58-XB1A4A-1.50=W58

TE Part #1-2329389-9
PB OFF/ON FC GRE M1 TERM GRE
LED IP68 50



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1423696-5_O.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1423696-5_O.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1423696-5_O.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

W54 Push To Reset Only Thermal Circuit Breaker

English

Industrial Relays Quick Reference Guide

English

Industrial Relays Quick Reference Guide

Japanese

Industrial Relays Quick Reference Guide