



Agastat

TE Internal #: 1-1437488-7

Time Delay Relays, Knob, 60VDC Time Delay Relay Input Voltage, 10A@240VACA Time Delay Relay Contact Current Rating, On-Delay

[View on TE.com >](#)

Relays, Contactors & Switches > Relays > Time Delay Relays



Type of Control: **Knob**

Time Delay Relay Input Voltage: **60 VDC**

Time Delay Relay Contact Current Rating: **10A@240VAC A**

Mode of Operation: **On-Delay**

Delay Time: **20 – 200 seconds**

Features

Product Type Features

Product Type	Relay
Relay Type	Time Delay
Product Category	Electromechanical Relays
Magnetic Blow-Out Device	Without

Configuration Features

Multiple Timing Ranges	Without
------------------------	---------

Electrical Characteristics

Actuating System	DC
Time Delay Relay Input Voltage	60 VDC

Contact Features

Contact Arrangement	2 Form C, DPDT, 2 C/O
Type of Control	Knob
Time Delay Relay Contact Current Rating	10A@240VAC A
Delay Time	20 – 200 seconds

Termination Features

Termination Type	Screw Terminals
------------------	-----------------

Mechanical Attachment

--	--



Time Delay Relay Mounting Type

Mounting Bracket

Dimensions

Dimensions (L x W x H) (Approximate)

114.8 x 82.55 x 78.48 mm[4.52 x 3.25 x 3.09 in]

Usage Conditions

Operating Temperature Range

-30 – 75 °C

Operation/Application

Option

Double Quick Connect Terminals, Tamper-Proof Cap - Transparent

Mode of Operation

On-Delay

Other

Repeatability (Max)

±5%

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU

Not Compliant

EU ELV Directive 2000/53/EC

Not Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2021 (211)
Candidate List Declared Against: JAN 2021 (211)
Does not contain REACH SVHC

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # 2-1423162-9
7022BK=RLY,STD,OFF,M2P,240VAC,

Customers Also Bought



TE Part #8-1437487-6
7012ODILL=24V DC 5-50 SEC



TE Part #5677604005
RNF-3000 Single Wall Spool HS Tubing



TE Part #183024-1
AMP SUPERSEAL 1.5MM,
RECEPTACLE AND TAB




TE Part #927770-3
TIMER, RECEPTACLE AND TAB



TE Part #7574442007
RAYRIM-NR8-0-STK



TE Part #5053264039
RNF-100-3/4-4-SP



TE Part #8-1623933-0
CFR50 5% 9K1



TE Part #4-1423161-8
7014RHA2I2=RLY,STD,ON,4P,60V,30M,
A2,I2



TE Part #4-1755142-8
7022RHA2I=RLY,STD,OFF,2P,60V,30M,
A2,I

Documents

Product Drawings

7012REA2I=60V DC 20-200 SEC

English

Datasheets & Catalog Pages

5-1773450-5_sec12_7000

1-1437488-7

Time Delay Relays, Knob, 60VDC Time Delay Relay Input Voltage, 10A@240VACA
Time Delay Relay Contact Current Rating, On-Delay



English