




Terminals & Splices > Ring Terminals & Spade Terminals



Terminal & Splice Type: **Ring Tongue**

Wire Size: **509 – 3260 CMA**

Ring & Spade Stud Size: **#6, M3.5**

Features

Product Type Features

Terminal Features	Slotted
Shape Description	Slotted Ring-002
Ring & Spade Stud Size	#6, M3.5
Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	No
Ring & Spade Wire/Cable Type	Regular Wire
Support Style	Non - Insulation Support

Configuration Features

Terminal Angle	Straight
----------------	----------

Body Features

Weight per Piece	.394 g
Ring & Spade Plating Material	Copper, Tin

Contact Features

Terminal & Splice Type	Ring Tongue
Ring & Spade Terminal Orientation	Straight

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	509 – 3260 CMA
-----------	----------------



Stud Diameter	3.51 mm[.138 in]
Tongue Thickness	.79 mm[.031 in]
Ring & Spade Overall Length	10.74 mm[.423 in]
Barrel Inside Diameter	1.55 mm[.061 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	170 °C[338 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	1000
Ring & Spade Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits



as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 49935 DAHT SOLIS 22-10 ASSY	 TE Part # 539662-2 MATR SOLISTR 0,3-6,	 TE Part # 47812 DIES SOLIS 22-16 DIE SET	 TE Part # 169400 CERTI-LOK
--	--	---	---

Customers Also Bought

 TE Part #179228-6 AMP COMMON TERMINATION HOUSINGS	 TE Part #103653-4 05 MTE SHRD PIN HSG SR LATCH	 TE Part #280361 AMPMODU II REC. HSG, SINGLE ROW 8 POS	 TE Part #175104-2 MULTILOCK, RECEPTACLE AND TAB
 TE Part #TAB62535501-080 Fieldbus,PROFIBUS M12B2 PUR DragChain DE	 TE Part #2592854002 NETM1000-14-0-SP	 TE Part #172494-1 MIC MARK-2 PLUG HSG 5P	 TE Part #1-406525-1 IMJ,NO SHLD,8P,TRAY, SN
 TE Part #2-1532179-3 M83513/03-A07C, MCKS-C2-B-9P5L5-0.5	 TE Part #1366094002 NETM1000-10-0-SP		

Documents

Product Drawings
SOLIS SLTD 22-16COMM 22-18MIL6

English



Agency Approvals

UL Report

English

UL Report

English