




Relays, Contactors & Switches > Switches > Slide Switches



Configuration (Pole-Throw): **Four Pole - Double Throw**

Slide Switch Mounting Angle: **Vertical**

Contact Base Material: **Copper Alloy**

Number of Actuators: **Single**

Number of Slide Switch Positions: **4**

Features

Product Type Features

Threaded Case	Without
Grade	Telecom
Switch Type	Slide
Product Type	Switch
Switch Style	Auto-Insertable
Terminal Configuration	Standard
Actuator Style	Extended, Top

Configuration Features

Configuration (Pole-Throw)	Four Pole - Double Throw
Number of Actuators	Single
Number of Slide Switch Positions	4
Operating Function	On On

Electrical Characteristics

Slide Switch Voltage Rating (VDC)	28
Slide Switch Voltage Rating (VAC)	115

Body Features

Actuator Material	Nylon
Actuator Color	White



Contact Features

Contact Base Material	Copper Alloy
Slide Switch Contact Current Rating	.3 A
Switch Contact Plating Material	Silver

Termination Features

Termination Type	PC
------------------	----

Mechanical Attachment

PCB Mount Retention	Without
Slide Switch Mounting Angle	Vertical
Slide Switch Mounting Type	Through Hole

Dimensions

PCB Tail Length	4.06 mm[.16 in]
Actuator Length	2.79 mm[.11 in]
Width	7.37 mm[.29 in]
Length	17.78 mm[.7 in]

Identification Marking

Stamped Marking	With
-----------------	------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Tube
------------------	------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (13% in Component Part) <small>Article Safe Usage Statements:</small>

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Not Low Halogen - contains Br or Cl > 900 ppm.

Solder Process Capability

Wave solder capable to 265°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | [Alcoswitch ASE/F](#)



Slide Switches(63)

Customers Also Bought



TE Part #1-745492-9
IDC D-Sub: Plug Assembly, Wire to Wire, Signal, 2.77 mm



TE Part #1-5102156-1
AMP-LATCH UNIVERSAL HEADERS



TE Part #1-534998-0
20 MODIV VRT DR CE 100/125



TE Part #104130-5
026 LOPRO HDR RA 30DP LATCH



TE Part #1-2213764-9
AV19 SPM 5A FIX RING LED BLUE 24V



TE Part #2-102617-3
50 MODII HDR DRRA SHRD .100CL



TE Part #103149-8
16 MODII HDR DRRA B/A .100CL



TE Part #1-2213764-5
AV19 SPM 5A FIX RING LED GREEN 24V



TE Part #104074-5
25 SYSTEM 50 HDR SRRA SHRD



TE Part #RP102BT24P10
RTD PROBE ASSEMBLY

Documents

Product Drawings

[ASE42=4PDT AUTO-SLIDE](#)

English

Product Environmental Compliance

[TE Material Declaration](#)

English