



CII

TE Internal #: 1-1617806-5

Time Delay Relays, Fixed, 28VDC Time Delay Relay Input Voltage, 115VACA / 10A@28VDCA Time Delay Relay Contact Current Rating, Delay on Release

[View on TE.com >](#)

Relays, Contactors & Switches > Relays > Time Delay Relays



Type of Control: **Fixed**

Time Delay Relay Input Voltage: **28 VDC**

Time Delay Relay Contact Current Rating: **10A@28VDC A, 115VAC A**

Mode of Operation: **Delay on Release**

Delay Time: **60 seconds**

Features

Product Type Features

Enclosure Type	Hermetic Sealed Metallic
Product Type	Relay
Relay Type	Time Delay
Product Category	Electromechanical Relays
Magnetic Blow-Out Device	Without

Configuration Features

Status Indicator Type	None
Multiple Timing Ranges	Without

Electrical Characteristics

Actuating System	DC
Time Delay Relay Input Voltage	28 VDC

Contact Features

Contact Arrangement	2 Form C, DPDT, 2 C/O
Contact Base Material	Silver Cadmium Oxide
Type of Control	Fixed
Time Delay Relay Contact Current Rating	10A@28VDC A, 115VAC A
Delay Time	60 seconds

Termination Features



Termination Type	Solder Pin Terminal
------------------	---------------------

Mechanical Attachment

Time Delay Relay Mounting Type	Raised Vertical Flange Mount
--------------------------------	------------------------------

Dimensions

Dimensions (L x W x H) (Approximate)	25.79 x 25.79 x 25.4 mm[1.015 x 1.015 x 1 in]
--------------------------------------	---

Usage Conditions

Operating Temperature Range	-55 – 125 °C
-----------------------------	--------------

Operation/Application

Mode of Operation	Delay on Release
-------------------	------------------

Other

Repeatability (Max)	±10%
---------------------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not lead free process capable

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



TE Part # 2-1617749-2
FCA-210-1024M=M83536/10-024M

Customers Also Bought



TE Part #397892-000
RMW-16/5-1200/ADH-0



TE Part #1-1437559-2
MTG106E=(MSTG) SW TOG MUSTANG



TE Part #8-1617807-4
TD229-5001P=TD5R 5 SEC M83726/29-5001P



TE Part #1-608036-2
SILICONE FUSION TAPE, 1"X36'



TE Part #1241380-3
AMP MCP, RECEPTACLE AND TAB



TE Part #467449-000
S03-04-R-9035-100



ANVIL
REPRESENTATION ONLY

TE Part #1-1803000-4
ANVIL, COMBINATION, END FEED



TE Part #066671-000
55A1832-14-MST3-9CS2275



TE Part #6-1633383-0
ANVIL, COMBINATION

TE Part #ZPF000000000015364
DMC-M 80-01

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1617806-5_A.2d_dxf.zip

English



Customer View Model

[ENG_CVM_CVM_1-1617806-5_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1617806-5_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[High_Performance_Relays_Section5](#)

English