



**Kilovac**

TE Internal #: 1-1618013-4

High Voltage Relays, .25kVDC Contact Voltage Rating, High Voltage Relay Contact Arrangement 1 Form X, SPST-NO-DM, Stud Terminals, Stud Terminals

[View on TE.com >](#)

Relays, Contactors & Switches > Relays > High Voltage Relays



Contact Voltage Rating: **.25 kVDC**

High Voltage Relay Contact Arrangement: **1 Form X, SPST-NO-DM**

High Voltage Connection (Coil): **Stud Terminals**

High Voltage Connection (Power): **Stud Terminals**

Economizer: **Without**

**Features**

**Product Type Features**

RF Rated	No
Product Type	Relay
Relay Type	High Voltage

**Configuration Features**

Economizer	Without
Power Switching	Yes

**Electrical Characteristics**

Contact Voltage Rating	.25 kVDC
High Voltage Relay Voltage (Max)	320 VDC
High Voltage Relay Coil Voltage Rating	24 VDC
High Voltage Relay Coil Resistance	52 Ω
High Voltage Relay Contact Switching Voltage (Max)	250

**Contact Features**

High Voltage Relay Contact Arrangement	1 Form X, SPST-NO-DM
Auxiliary Contacts	Without
High Voltage Relay Contact Current Rating	500 A

**Termination Features**

High Voltage Connection (Coil)	Stud Terminals
--------------------------------	----------------



High Voltage Connection (Power)	Stud Terminals
Termination Style	Stud Terminals

**Mechanical Attachment**

High Voltage Relay Mounting Type	Panel Mount
----------------------------------	-------------

**Product Compliance**

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

**Compatible Parts**



TE Part # 1618002-7  
EV200AAANA=RELAY, EV200 SPST-N

## Customers Also Bought




TE Part #2-322329-1  
TERM, RING, STRATO-THERM, HT, 16-14, 6



TE Part #696420-5  
TERMINAL,PIDG PVF2 R 26-24 8



TE Part #808489-000  
Low Profile Heat Shrink Boots: Poly Molded, Lipped, Straight



TE Part #208870-1  
PLUG ASSY,78 POSN,AMPLIMITE



TE Part #3-1617351-6  
JMACDG-26XP=M39016/15-093P



TE Part #YDTS26G11-02PNV001  
D38999: Straight Plug, 11-02 Insert



TE Part #440703-000  
SO63-1-9030



TE Part #448153-2  
PLUG ASSY,SZ 2,COAX 3C3, NM



TE Part #445705-5  
AMPLIMITE,RCPT ASY,3C3,2,NM



TE Part #2-1393766-7  
R10-E1X8-V350=R10

## Documents

### Product Drawings

PD150XB57=RELAY, VACUUM, SPST-

English

### Datasheets & Catalog Pages

RELAY, VACUUM, SPST

English