350591-1 ✔ ACTIVE


AMP

TE Internal #: 350591-1

Rectangular Connector Keying Plugs, Keying Plug, 1 Position, Power & Signal, Operating Temperature Range -55 – 105 °C [-67 – 221 °F]

View on TE.com >

Connectors > Rectangular Connectors > Rectangular Connector Accessories > Rectangular Connector Keying Plugs



Connector Keying Accessory Type: **Keying Plug**

Number of Positions: **1**

Circuit Application: **Power & Signal**

Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**

Features

Product Type Features

Product Type	Accessory
Connector Keying Accessory Type	Keying Plug

Configuration Features

Number of Positions	1

Body Features

Material	PA 66
Color	Black

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Operation/Application

Circuit Application	Power & Signal

Industry Standards

UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Method	Loose Piece
Packaging Quantity	5000

Other

Comment	Use in socket housings only.

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2020 (205) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts




TE Part # 1-640517-0
02P MR II PLUG HSG


Customers Also Bought




TE Part #1-644042-2
Nylon Gold Plated Receptacle: 2.54 mm, With Mating Alignment, MTA 100



TE Part #1-640514-0
20P MR II CAP HSG V0 RED



TE Part #1-640519-0
04P MR II PLUG HSG V0 RED



TE Part #1-640526-0
36P MR II PLUG HSG V0 RED



TE Part #1-770254-0
UMNL II GROUND PIN LP DUPL BR




TE Part #1-747946-5
IDC D-Sub: Connector Kit, Plug, Wire to Wire, Signal, 2.77 mm




TE Part #1445826-1
MINI CPC



TE Part #1-456402-6
CRIMPER WIRE .055 F



TE Part #1-480594-9
36P STR/REL HNGD BLK



TE Part #805278-1
ANVIL, COMBINATION

Documents

Product Drawings

MR KEYING PLUG BR/RED

English

CAD Files

Customer View Model

ENG_CVM_350591-1_D.3d_igs.zip

English

Customer View Model

ENG_CVM_350591-1_D.3d_stp.zip

English

Customer View Model

ENG_CVM_350591-1_D.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

SOFT_SHELL_PIN_AND_SOCKET_CONNECTORS_CATALOG

English