



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal & Splice Type: **Tab**
Housing Type: **Tab Housing**
Number of Crimp Terminal Housing Positions: **1**
Crimp Terminal Housing Terminal Orientation: **Straight**
Crimp Terminal Housing Housing Color: **Natural**

Features

Product Type Features

Product Type	Terminal Housing
Terminates To	Wire & Cable
Connector System	Wire-to-Wire
Housing Type	Tab Housing
Sealable	No
Insulated	No

Configuration Features

Number of Crimp Terminal Housing Positions	1
--	---

Body Features

Crimp Terminal Housing Housing Color	Natural
Crimp Terminal Housing Mating Retention	With
Crimp Terminal Housing Mating Alignment	With

Contact Features

Terminal & Splice Type	Tab
------------------------	-----



Crimp Terminal Housing Terminal Orientation	Straight
---	----------

Mechanical Attachment

Mating Alignment Type	Polarization
Mating Retention Type	Latch
Crimp Terminal Housing Mounting Style	Cable Mount (Free-Hanging)

Housing Features

Crimp Terminal Housing Housing Material	Nylon
---	-------

Dimensions

Length	9.65 mm[.38 in]
Width	6.35 mm[.032 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

For Use With	FASTON Terminals
--------------	------------------

Packaging Features

Packaging Quantity	1
Crimp Terminal Housing Packaging Method	Carton

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 360041-1 187 FASTON HSG.,TAB,1 POS, NATURAL	 TE Part # 881339-2 SLEEVE FASTON 250 TAB NATURAL PA.6.6 V.0	 TE Part # 881339-3 SLEEVE FASTON 250 TAB NATURAL PA.6.6 V.0	 TE Part # CAT-P9426-A79 CLASS II, UL 1585, 40VA CONTROL TRANSFS
 TE Part # CAT-P9426-A87 CLASS II, UL 1585, 75VA CONTROL TRANSFS	 TE Part # CAT-P9426-A84 CLASS II, UL 1585, 50VA CONTROL TRANSFS	 TE Part # CAT-P9426-A16 10 VA TRANSFORMERS	 TE Part # CAT-P9426-A75 CLASS II, UL 1585, 30VA CONTROL TRANSFS
 TE Part # CAT-P9426-A15 GENERAL PURPOSE UL 506, 100VA TRANSFS	 TE Part # CAT-P9426-A19 GENERAL PURPOSE UL 506, 150VA TRANSFS	 TE Part # 8-1611470-5 4700-26EW30BB999=TRANSFORMER	 TE Part # 1611448-7 4100-102J15AE999=TRANSFORMER

Also in the Series | FASTON 250





Compression Connectors(4)



Crimp Terminal Housings(143)



Insertion & Extraction Tools(6)



Magnet Wire Terminals(1)



PCB Terminals(144)



Quick Disconnects(466)



Splices(4)

Customers Also Bought




TE Part #1-440054-0
AMP HPI 2.0MM HEADERS



TE Part #1-770849-2
3.96mm Wire-to-board housing: receptacle, with mating alignment, SL 156



TE Part #1393030-8
P&B SSR SERIES SOLID STATE RELAYS



TE Part #1-35115-0
SPLICE,N CE 22-14



TE Part #1217113-2
187 PL MKIII REC. 22-18AWG TPBR



TE Part #1419108-2
RT114012F



TE Part #1611434-2
98220-332=AUXILARY 1NO/1NC SWI



TE Part #G-TPMO-024
TSEV01C-W

Documents

Product Drawings
250 FASTON HSG.,TAB,1 POS,NATRUAL
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_360042-1_R.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_360042-1_R.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_360042-1_R.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[FASTON PCB Tabs and Receptacles](#)

English

[PRINTED CIRCUIT BOARD TERMINALS AND DISCONNECTS](#)

English

Product Specifications

[Product Specification](#)

English

Product Environmental Compliance

[MD_360042-1_061320181245_dmtec](#)

English

[MD_360042-1_061320181245_dmtec](#)

English

Agency Approvals

[UL Report](#)

English