



Connectors > Socket Connectors > IC Sockets > DIP Sockets > DIP Socket: Low Profile, Stamped & Formed, Open, Tin



Contact Fabrication: **Stamped & Formed**

Number of Positions: **16**

Connector Profile: **Low**

Row-to-Row Spacing: **7.62 mm [.3 in]**

PCB Mount Orientation: **Vertical**

[All DIP Socket: Low Profile, Stamped & Formed, Open, Tin \(6\)](#)

Features

Product Type Features

Leg Style	Straight
Connector & Contact Terminates To	Printed Circuit Board
Product Type	Socket

Configuration Features

Number of Positions	16
PCB Mount Orientation	Vertical
Number of Rows	2

Electrical Characteristics

Contact Resistance	20 mΩ
Insulation Resistance	1000 MΩ

Body Features

Sleeve Material	Brass/Copper
Sleeve Plating Material	Tin/Lead
Frame Style	Ladder
Connector Profile	Low
Color	Black



Contact Features

Socket Style	Standard
Mating Contact Type	Dual Leaf
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Phosphor Bronze
Contact Fabrication	Stamped & Formed
Contact Mating Area Plating Material	Tin
	60 μin
Contact Current Rating (Max)	1 A
Socket Type	DIP
Contact Type	Pin

Termination Features

Termination Method to Printed Circuit Board	Through Hole - Solder
	3 in

Mechanical Attachment

Connector Mounting Type	Board Mount
Mating Alignment Type	Polarization
Mating Alignment	With

Housing Features

Centerline (Pitch)	2.54 mm[.1 in]
Housing Material	PBT GF30

Dimensions

Height Above PC Board	5.1 mm[.2 in]
Row-to-Row Spacing	7.62 mm[.3 in]
	.8 in

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features



Tubes per Box	2
Packaging Method	Box & Tube, Tube
Packaging Quantity	30

Other

Quantity per Tube	3000
-------------------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 240°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought






TE Part #1-2199298-6
DIP Socket: Low Profile, Stamped & Formed, Open, Tin



TE Part #1-640456-0
Polyester Vertical PCB Header: 2.54 mm, Unshrouded, No Mating Alignment



TE Part #1-2199298-8
24P,DIP SKT,300 CL,LDR,PB FREE



TE Part #881545-2
SHUNT LP W/HANDLE 2 POS 30AU



TE Part #1-5331677-6
Mini Spring Sockets: Closed Bottom, 5A



TE Part #1-1625875-9
CBT 1/4 5% 220R



TE Part #1-2199299-5
DIP Socket: Standard, Stamped & Formed, Open, Tin

Documents

Product Drawings
16P,DIP SKT,300 CL,LDR,PB FREE
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_1-2199298-4_A.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_1-2199298-4_A.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_1-2199298-4_A.3d_stp.zip
English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages
DIP Sockets Quick Reference Guide (EN)
English

Product Environmental Compliance
Product Compliance
English
Product Compliance
English

1-2199298-4

DIP Sockets, Stamped & Formed, 16 Position, Low Connector Profile, Row-to-Row
Spacing .3 in [7.62 mm], Vertical, Straight, Tin

