


TE Internal #: 4-192038-0
Rectangular Contact Inserts, Socket, 1 Position, 120A Contact
Current Rating (Max), Power, Operating Temperature Range -196 –
200 °C [-320 – 392 °F]

[View on TE.com >](#)



Connectors > Rectangular Connectors > Rectangular Contact Inserts



Contact Type: **Socket**
Number of Positions: **1**
Sealable: **No**
Contact Current Rating (Max): **120 A**
Circuit Application: **Power**

Features

Product Type Features

Product Type	Contact
Sealable	No

Configuration Features

Number of Positions	1
---------------------	---

Body Features

Material	Beryllium Copper
----------	------------------

Contact Features

Contact Type	Socket
Contact Current Rating (Max)	120 A

Usage Conditions

Operating Temperature Range	-196 – 200 °C[-320 – 392 °F]
-----------------------------	------------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

TE Part # 4-192038-8
LA3,250,006,SILVER

Customers Also Bought

TE Part #206153-1
CPC SERIES 1

TE Part #1658646-1
D-Sub Crimp Recept Signal 9 Posn,
Socket Size 20, Shell Size 1TE Part #206070-8
CPC CABLE CLAMPSTE Part #1-5103309-0
A/L LOW PRO HDR 50P VERT BLACK



Documents

Product Drawings

[LA3\(.008\)GOLD](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_4-192038-0_L.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_4-192038-0_L.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_4-192038-0_L.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[POWER_CONNECTORS_CATALOG_SEC02_CABLE_MOUNTED](#)

English