




Connectors > PCB Connectors > PCB Connector Accessories > PCB Connector Keying



Connector Keying Accessory Type: **Keying Plug**
Operating Temperature Range: -55 – 105 °C [-67 – 221 °F]

Features

Product Type Features

Connector Keying Accessory Type	Keying Plug
---------------------------------	-------------

Body Features

Primary Product Material	Nylon 6/6
Primary Product Color	Natural

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-2
------------------------	----------

Packaging Features

Packaging Method	Bag
Packaging Quantity	2500

Other

Comment	Used with staked post.
---------	------------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-103156-RECHS
3.96mm Rectangular connector housing: 1 row, Nylon, SL 156



TE Part # CAT-103156-WBHSM
3.96mm Wire-to-board housing: receptacle, with mating alignment, SL 156



TE Part # 640254-1
KEYING PLUG .045 SQ PST CONN



TE Part # 2-2132074-0
20Pos SL156 Contact Retainer


Also in the Series | SL-156



Insertion & Extraction Tools(1)



PCB Connector Keying(2)



PCB Latches, Locks & Retainers(1)



Rectangular Connector Housings(12)



Rectangular Connector Keying Plugs(1)



Wire-to-Board Connector Assemblies & Housings(157)



Wire-to-Board Connector Contacts(24)

Customers Also Bought



TE Part #2-320855-1
TERMINAL,SOLIS SPD FLG 16-14 6




TE Part #CA1277-000
Dual Wall DWP-125 Spool HS Tubing



TE Part #1586843-1
01P UMNL CAP HSG NATL, GW



TE Part #2029388-1
04P UMNL SHORT LATCH PLUG GW



TE Part #521116-2
MOTOR HOUSING HOUSING NYLON VO BLACK



TE Part #521210-3
HSG,POS-LOC,MKIII,250SERIES,6P



TE Part #521498-4
FASTON 250 REC HSG 4 CIR BLK



TE Part #650048-1
9 POS DUO TYNE FLAG HSG



TE Part #680008-2
APPL,HDM,SPL 9EAPR080F1100 K



TE Part #3-1123722-4
3.96 EP PLUG HSG 4P(BLUE)

Documents



Product Drawings

KEYING PIN .045 SQ PST CONN

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_640255-1_J_c-640255-1-j.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_640255-1_J_c-640255-1-j.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_640255-1_J_c-640255-1-j.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

MTA 156 Ribbon Cable Connector Assemblies (English And Spanish)

English

Application Specification

English

Application Specification

Japanese

MTA 156 Ribbon Cable Connector Assemblies (English And Spanish)

Japanese

Agency Approvals

CSA Certificate

English