



TE Internal #: 0137310001

Printable Tubing, Ladder Printable Tubing Type, Commercial

Printable Tubing Grade, 3:1 Printable Tubing Shrink Ratio, White, 1

Prescore

[View on TE.com >](#)

Identification & Labeling > Printable Tubing



Printable Tubing Type: **Ladder**

Printable Tubing Grade: **Commercial**

Printable Tubing Shrink Ratio: **3:1**

Primary Product Color: **White**

Number of Prescores: **1**

## Features

### Product Type Features

Printable Tubing Type	Ladder
Printable Tubing Grade	Commercial

### Body Features

Printable Tubing Shrink Ratio	3:1
Primary Product Color	White
Markers per Sleeve	2

### Dimensions

Product Length	50 mm[2 in]
Supplied Inner Diameter	6.4 mm[.25 in]
Recovered Inside Diameter	2.11 mm[.083 in]
Compatible Cable Diameter Range	2.31 – 5.46 mm[.091 – .215 in]

### Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

### Operation/Application

Recommended Ribbon	See TE Document 411-121005 the Printer Product Ribbon Matrix
--------------------	--

### Printer/Label Features

Recommended Printer	See TE Document 411-121005 the Printer Product Ribbon Matrix
---------------------	--



Printer Technology	Thermal Transfer
Number of Prescores	1

**Packaging Features**

Packaging Quantity	250
--------------------	-----

**Product Compliance**

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

**Compatible Parts**

TE Part # 1-2186500-1  
T3212-PRINTER

TE Part # 1-2186502-1  
T3224-PRINTER

TE Part # 1-2186503-1  
T3224-SWARE-PRINTER

TE Part # CP8122-000  
T6112DS-PRINTER



TE Part # 1-2186501-1  
T3212-SWARE-PRINTER

## Customers Also Bought



TE Part #1-1825097-2  
TPB11FGRA204



TE Part #1-106506-2  
D-Sub Receptacle Assembly: Right Angle, Shell Size 2, 2.74mm



TE Part #1229590001  
RPS COMMERCIAL GRADE SLEEVES



TE Part #073937-000  
D-SCE FLUID RESISTANT SLEEVES




TE Part #1-1740196-2  
D-Sub Receptacle Assy: Eurostyle, Right Angle, Surface Mount, 2.74mm



TE Part #ZPF000000000007332  
983-0S 10-06 P6



TE Part #1-1393258-7  
V23047-A1024-A511



TE Part #1-1586040-0  
10P VAL-U-LOK VRT HDR W/P V0



TE Part #1130813001  
100G0111-2.50-45



TE Part #1423167-3  
SSFR90B=UNIV. TIMER 240V

## Documents

### Product Drawings

RPS-16-10/2.0-S1-9

English

### Datasheets & Catalog Pages

RPS Heat Shrinkable Sleeves

English

### Product Specifications

RPS



English

---

[Instruction Sheets](#)

[Instruction Sheet \(non U.S.\)](#)

English