




Connectors > Socket Connectors > IC & Component Socket Accessories > Heat Sinks



Device Type: BGA

Fin Style: Radial

Number of Fins: 4

Power: 5 W, 10 W, 15 W

Features

Product Type Features

Device Type	BGA
Accessory Type	Clip

Configuration Features

Number of Fins	4
----------------	---

Electrical Characteristics

Power	5 W, 10 W, 15 W
-------	-----------------

Body Features

Fin Style	Radial
Material	Aluminum
Plating Material	Black Anodized

Industry Standards


UL Flammability Rating	UL 94V-0
------------------------	----------

Other

Air Velocity	0 LFM, 200 LFM, 400 LFM, 600 LFM
Comment	Heat sink assembly includes Three Leg Standard Clip, Part Number 1542816-1., Mounting clip does not increase overall heat sink height.

Product Compliance

For compliance documentation, visit the product page on TE.com>






EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # CAT-D625-80007

DIP Socket: Standard, Stamped & Formed, Open, Gold

Customers Also Bought





TE Part #2007399-5
SFP+ Stacked Cage Assemblies



TE Part #2291634-1
SFP+ 1X1 CAGE ASSY, PF,WITH HEATSINK



TE Part #7-2176414-5
7W STD M/OX 5% 24K



TE Part #2007820-2
IMP100S,H,V4P10C,UG,OEWS39,4.9



TE Part #1622925-1
CRG0603 1% 360K



TE Part #2057419-2
IMP100S,H,V2P10C,LG,OEWS39,4.9



TE Part #3-825433-2
MOD 2 PINHDR 1X32P.



TE Part #2291634-2
SFP+ 1X1 CAGE ASSY, PF,WITH HEATSINK



TE Part #1658912-5
ASSY, 0.00038MIN AU 3.18 TAIL



TE Part #3-1367703-2
R/A AMC Conn,Style B+,Sn,w/Hdw

Documents

Product Drawings
29MM HEAT SINK ASS'Y

English

Product Specifications
Application Specification

English

Product Environmental Compliance
TE Material Declaration

English