

W54-XB1A4A10-25 ✓ ACTIVE

Potter & Brumfield W54

TE Internal #: 1-1423674-0

Potter & Brumfield W54, Circuit Breakers, Thermal, Series Trip, White with Red Rate Marking (Vertical) Button Color, 250VAC Voltage Rating AC

[View on TE.com >](#)



Relays, Contactors & Switches > Circuit Breakers



Circuit Breaker Type: **Thermal**

Circuit Function: **Series Trip**

Illuminated: **No**

Button Color: **White with Red Rate Marking (Vertical)**

Voltage Rating AC: **250 VAC**

Features

Product Type Features

Illumination Type	No Light
Product Type	Circuit Breaker
Actuator Type	Push to Reset
Circuit Breaker Type	Thermal
Illuminated	No

Configuration Features

Panel Cutout	11.2 x 10.01 mm [.441 x .394 in]
Earthing Switch	Without
Circuit Function	Series Trip

Electrical Characteristics

Voltage Rating AC	250 VAC
Voltage Rating DC	50 VDC
Circuit Breaker Current Rating	25 A
Interrupt Capacity	1000A @ 250VAC/50VDC

Body Features

Button Color	White with Red Rate Marking (Vertical)
--------------	--

Contact Features

Pole Configuration	1
--------------------	---



Trip Time at 200% 5 – 30 seconds

Termination Features

Circuit Breaker Termination Type 6.35 [.25] Straight Quick Connect Tab

Mechanical Attachment

Mounting Hardware Packaging Assembled to Bushing

Mounting Options Knurled Nut/Hex Nut

Mounting Bushing 9.8 x 12.6mm Long, Metal

Circuit Breaker Mounting Type Panel Mount

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU Compliant

EU ELV Directive 2000/53/EC Not Compliant

China RoHS 2 Directive MIIT Order No 32, 2016 No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006
 Current ECHA Candidate List: JAN 2021 (211)
 Candidate List Declared Against: JUN 2018 (191)
 SVHC > Threshold:
 Not Yet Reviewed

Halogen Content Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | Potter & Brumfield W54



Customers Also Bought





Documents

CAD Files

Customer View Model

[ENG_CVM_1-1423674-0_1108.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_1-1423674-0_1108.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_1-1423674-0_1108.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[W54 Push To Reset Only Thermal Circuit Breaker](#)

English

[Industrial Relays Quick Reference Guide](#)

English

[Industrial Relays Quick Reference Guide](#)

Japanese

[Industrial Relays Quick Reference Guide](#)