



Fiber Optics > Fiber Optic Connectors > Rugged Fiber Connectors > Expanded Beam Fiber Optics



Expanded Beam Fiber Optic Product Type: **Ferrule Kit**

Expanded Beam Fiber Optic Fiber Diameter: **126 μm**

Expanded Beam Fiber Optic Mode: **Singlemode**

Features

Product Type Features

Expanded Beam Fiber Optic Product Type	Ferrule Kit
Expanded Beam Fiber Optic Mode	Singlemode

Dimensions

Expanded Beam Fiber Optic Fiber Diameter	126 μm
--	--------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these

limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 1374759-2
INSERT ASSY, 4XMM, MINI



TE Part # 1374759-4
INSERT ASSY, 2XMM, MINI



TE Part # 1374759-1
INSERT ASSY W/ FLATS, 4XMM, MINI



TE Part # 1374759-3
INSERT ASSY W/ FLATS, 2XMM, MINI

Also in the Series | CGS SM



Battery Holders(1)



Expanded Beam Fiber Optics(9)



LC Connectors(2)




RJ14 Connectors(1)




RJ22 Connectors(1)



RJ25 Connectors(1)



RJ45 Connectors(3)




SD Card Connectors(1)



Surface Mount Resistors(545)

Customers Also Bought



Documents

Product Drawings

[FERRULE KIT, SM, 126, MINI EB](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1754700-2_D.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1754700-2_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1754700-2_D.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

[Instruction Sheet \(U.S.\)](#)

English

[Instruction Sheet \(U.S.\)](#)

English



Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English