



Application Tooling > Portable Crimp Tools



Tool Grade: **Commercial Crimp Tooling**
Ratchet Configuration: **Operator Releasable & Adjustable**
Die Sets Type: **Fixed In Tool**
Specification Type: **TE Product Specification (114-)**
TE Certification: **Upon Request for Fee**

Features

Other

Crimp Form-Wire Barrel Type	Open Barrel - F Crimp
Tool Grade	Commercial Crimp Tooling
Ratchet Configuration	Operator Releasable & Adjustable
Die Sets Type	Fixed In Tool
Specification Type	TE Product Specification (114-)
TE Certification	Upon Request for Fee
Power Technology Type	Manual
Tooling Type	Straight Action Hand Tool

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUL 2019 (201) SVHC > Threshold: Not Yet Reviewed



Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-1987559-1 PHOTOVOLTAIK CONNECTOR, 4sqmm	 TE Part # 1-1987559-2 PHOTOVOLTAIK CONNECTOR, 4sqmm	 TE Part # 1987281-3 HVT SOCKET CONTACT 10 AWG, ASSY	 TE Part # 5-1105300-1 HVT-C-Sti.Ag,4,0 qmm
 TE Part # 5-1105301-1 HVT-C-Bu.Ag,4,0 qmm	 TE Part # 1-1987558-1 PHOTOVOLTAIK CONNECTOR, 4sqmm	 TE Part # 1-1987558-2 PHOTOVOLTAIK CONNECTOR, 4sqmm	 TE Part # 1-1987558-3 PHOTOVOLTAIK CONNECTOR, 4sqmm
 TE Part # 7-1105300-2 HVT-C-Sti.Ag.AWG.10	 TE Part # 7-1105301-2 HVT-C-Bu.Ag.AWG.10		

Customers Also Bought



 TE Part #1-2176231-2 SMD Power Resistor: 3 Watt, 1% Tol	 TE Part #1-1987559-1 PHOTOVOLTAIK CONNECTOR, 4sqmm	 TE Part #1-1987559-2 PHOTOVOLTAIK CONNECTOR, 4sqmm	 TE Part #180916 FF 250 TAB HSG 1P NYLON NAT
 TE Part #1102855-3 AWZG-HVT-RSZ	 TE Part #1-2176342-9 CRGCQ 0805 1K0 5%	 TE Part #1624215-2 23SE 1MB 6.35X50FL B7 DPST (4A)	 TE Part #1625862-2 RH73 2A 20G 30% 1000PPM
 TE Part #1-1419126-8 STD OEG PCB PCFN Solar Power Relays	 TE Part #F40876-000 B-155-9002		

Documents

Product Drawings

CSV10 CRIMPING HANDTOOL SOLARLOK 4-6

English

Datasheets & Catalog Pages

CERTI-CRIMPII-Premium-August-1-1773864-7

English

CONNECTIVITY_SYSTEMS_FOR_PV_INSTALLERS_3-1773458-6

English

SOLARLOK_CONNECTIVITY_SYSTEMS_FOR_PV_MANUFACTURERS_3-1773458-7

English

AMERICAS_VERSION_SOLARLOK_INSTALLATION_MANUAL_2-1773458-2

English

Crimp Term Whitepaper-Use the Right Tool 1-1773953-1

English

Bottoming Dies

English

CRIMPING WHERE FORM MEETS FUNCTION



English

6-1773461-4_SOLARLOK_1-RAIL_JUN_BOX_CH

Product Specifications
INSTRUCTION SHEET

English

Instruction Sheets
Instruction Sheet (non U.S.)

English