



Relays, Contactors & Switches > Switches > Slide Switches



Configuration (Pole-Throw): **Double Pole - Double Throw**

Slide Switch Mounting Angle: **Vertical**

Contact Base Material: **Copper Alloy**

Number of Actuators: **Single**

Number of Slide Switch Positions: **2**

Features

Product Type Features

Threaded Case	Without
Grade	Instrumentation
Switch Type	Slide
Product Type	Switch
Terminal Configuration	Standard
Actuator Style	Extended, Top

Configuration Features

Terminals Connected	2-1, 5-4
Configuration (Pole-Throw)	Double Pole - Double Throw
Number of Actuators	Single
Number of Slide Switch Positions	2
Operating Function	On On

Electrical Characteristics

Slide Switch Voltage Rating (VAC)	125
-----------------------------------	-----

Body Features

Actuator Travel	2 mm[.079 in]
Actuator Material	POM
Actuator Color	Black



Contact Features

Contact Base Material	Copper Alloy
Slide Switch Contact Current Rating	.3 A
Switch Contact Plating Material	Silver

Termination Features

Termination Type	PC
------------------	----

Mechanical Attachment

PCB Mount Retention	With
PCB Mount Retention Type	Guide Post
Slide Switch Mounting Angle	Vertical
Slide Switch Mounting Type	Through Hole

Dimensions

PCB Tail Length	3.5 mm[.137 in]
Actuator Length	11 mm[.433 in]
Width	5.8 mm[.227 in]
Length	14 mm[.547 in]

Identification Marking

Stamped Marking	With
-----------------	------

Industry Standards

UL Flammability Rating	UL 94-HB
------------------------	----------

Packaging Features

Packaging Method	Tray
------------------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2016 (169) SVHC > Threshold: Not Yet Reviewed



Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
-----------------	--

Solder Process Capability	Wave solder capable to 265°C
---------------------------	------------------------------

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1825258-2
SPDT SL SW R/A AU



TE Part # 1825255-5
MHS12304=SPDT SL SW VERT AG



TE Part # 1825255-7
MHS13304=SP3T SL SW VERT AG



TE Part # 1825255-8
MHS133G04=SP3T SL SW VERT AU



TE Part # 1825257-1
MSS120004=SPDT SL SW VERT AG

Also in the Series | Alcoswitch MSS



Slide Switches(20)



Customers Also Bought



TE Part #1-2199298-6
DIP Socket: Low Profile, Stamped & Formed, Open, Tin



TE Part #1-5177986-2
Free Height Plug Connector: Board-Board, Vertical, 60, 0.8mm



TE Part #106740-4
160P.IEC-C.M.CONN.



TE Part #9-1676481-6
CPF 0603 82K 0.1% 25PPM 1K RL



TE Part #1-1337541-0
BNC Ins Str PCB Skt 50Ohm White



TE Part #1-1634505-0
BNC Ins Str PCB Skt 50Ohm Black



TE Part #103904-1
02 MTE HDR SRRA LATCH W/HLDWN



TE Part #1614349-2
RN 0603 100R 0.1% 10PPM CUT LE



TE Part #1622180-1
LR0204 1% 1K0



TE Part #1-5353187-0
.6FHP08H,140,S,STD,08/Sn,TR,NSYes

Documents

Product Drawings
MSS225004=DPDT SL SW VERT AG
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_1825263-1_A.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_1825263-1_A.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_1825263-1_A.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



Product Environmental Compliance
TE Material Declaration

English