

# SSR-240D25 ✓ ACTIVE

Potter & Brumfield | Potter & Brumfield SSR

TE Internal #: 1393030-7

Potter & Brumfield SSR, Power Relays, Solid State, Contact Arrangement 1 Form A (SPST-NO), Chassis Mount Relay Mounting Type

[View on TE.com >](#)



Relays, Contactors & Switches > Relays > Power Relays > P&B SSR SERIES SOLID STATE RELAYS



Power Relay Type: **Solid State**

Contact Arrangement: **1 Form A (SPST-NO)**

Relay Mounting Type: **Chassis Mount**

[All P&B SSR SERIES SOLID STATE RELAYS \(10\)](#)

## Features

### Product Type Features

Output Type	AC
Power Relay Type	Solid State

### Configuration Features

Output Switching	Zero
------------------	------

### Electrical Characteristics

Input Voltage Typical	3 – 32 VDC
Output Voltage (Max)	280 V
Output Voltage Rating (AC Relays)	24 – 280 Vrms
Output Current Rating	.1 – 25 Arms
Output Current (Min)	.1 A

### Body Features

Product Weight	98 g[3.45 oz]
Case Color	Black

### Contact Features



Switch Arrangement	1 Form A (SPST-NO)
--------------------	--------------------

Contact Arrangement	1 Form A (SPST-NO)
---------------------	--------------------

### Termination Features

Relay Termination Type	Screws
------------------------	--------

### Mechanical Attachment

Coupling	Optical
----------	---------

Relay Mounting Type	Chassis Mount
---------------------	---------------

### Housing Features

Relay Housing Style	Hockey Puck
---------------------	-------------

### Dimensions

Dimensions (L x W x H) (Approximate)	45 x 57.8 x 36.5 mm [1.772 x 2.276 x 1.437 in]
--------------------------------------	--

### Usage Conditions

Operating Temperature Range	-30 – 80 °C
-----------------------------	-------------

### Operation/Application

R-Switch & slimSSR Relays	No
---------------------------	----

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
------------------------------	---------------------------

EU ELV Directive 2000/53/EC	Compliant with Exemptions
-----------------------------	---------------------------

China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
---	--------------------------------------

EU REACH Regulation (EC) No. 1907/2006	<p>Current ECHA Candidate List: JAN 2021 (211)</p> <p>Candidate List Declared Against: JAN 2021 (211)</p> <p>SVHC &gt; Threshold:</p> <p>Pb (88% in Component Part)</p>
--	---

**Article Safe Usage Statements:**  
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Wave solder capable to 260°C
---------------------------	------------------------------



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



## Also in the Series | Potter & Brumfield SSR



## Customers Also Bought





TE Part #1-66360-1  
III+ SKT,18-14,30AU/FL,SMPACK



TE Part #1-1825138-5  
A201P3ZQ04



TE Part #1-87456-2  
16 MODIV HSG DR MRKD .100CL



TE Part #1-1609112-2  
CORCOM C SERIES IEC UNFILTERED INLETS



TE Part #1-1393143-9  
27E166=SOCKET, KH, 14, SCW, PLES



TE Part #1-1419106-9  
27E487=SOCKET, K10, 8, SCW, PHEN, G

## Documents

### CAD Files

#### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1393030-7\\_B.2d\\_dxf.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1393030-7\\_B.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1393030-7\\_B.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

#### SSR Hockey Puck Solid State Relay With Paired SCR Output

English

#### SSR, SSRD and SSRT Series

English

#### Industrial Relays Quick Reference Guide

English

#### Industrial Relays Quick Reference Guide

Japanese

#### Industrial Relays Quick Reference Guide