



Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2013 (144) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts




TE Part # 1393143-7
27E123=SOCKET,KRP,11,SCW,PLE




TE Part # 2-1419106-4
27E892=SOCKET,KRPA,11,OCTAL,PO

Also in the Series | Potter & Brumfield KRPA




Power Relays(60)



Relay Accessories, Sockets & Clips(5)

Customers Also Bought




TE Part #1SNK506013R0000
ZS4-R2



TE Part #4-1393117-1
KUP-11DT5-24=KU




TE Part #650950-5
150 EURO TYPE C PIN ST ASSY



TE Part #646480-2
2MM H.M., C SHROUD 3.9MM



TE Part #1423117-3
KUEP-11D35-110=RELAY,GENPUR,QC



TE Part #284726-1
ASS'Y COVER 60 POS AND CPA



TE Part #6367582-1
ASSY Z-DOK+4 ADAPTER BRD 16PR



TE Part #DIV43E21-35SN-023
RECP ASSY



TE Part #1676690-1
RN 0805 36R5 0.1% 10PPM CUT LENGTH



TE Part #3-1393253-3
W68-X2Q12-2=M6/M7/M9/W6/W7



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1393102-2_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1393102-2_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1393102-2_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

KRPA, KRP, KA, KR 5 to 10 Amp General Purpose Relay

English

Industrial Relays Quick Reference Guide

English

Industrial Relays Quick Reference Guide

Japanese

Industrial Relays Quick Reference Guide

Product Specifications

Definitions, Handling, Processing, Testing and Use of Relays

English