

T77S1D10-12

✓ ACTIVE

OEG

TE Internal #: 1393194-9
Power Relays, Standard, Monostable, DC, 400 – 500mW Coil Power
Rating Class, 450mW Coil Power Rating DC, 320Ω Coil Resistance
[View on TE.com >](#)



Relays, Contactors & Switches > Relays > Power Relays



Power Relay Type: **Standard**
Coil Magnetic System: **Monostable, DC**
Coil Power Rating Class: **400 – 500 mW**
Coil Power Rating DC: **450 mW**
Coil Resistance: **320 Ω**

Features

Product Type Features

Power Relay Type	Standard
------------------	----------

Electrical Characteristics

Insulation Initial Dielectric Between Coil & Contact Class	3500 – 4000 V
Insulation Initial Dielectric Between Open Contacts	750 Vrms
Contact Limiting Making Current	10 A
Contact Limiting Short-Time Current	10 A
Contact Limiting Continuous Current	10 A
Insulation Creepage Class	5.5 – 8 mm
Insulation Initial Dielectric Between Contacts & Coil	4000 Vrms
Insulation Creepage Between Contact & Coil	6.4 mm[.252 in]
Contact Limiting Breaking Current	10 A
Coil Magnetic System	Monostable, DC
Coil Power Rating Class	400 – 500 mW
Coil Power Rating DC	450 mW
Coil Resistance	320 Ω



Coil Special Features	UL Coil Insulation Class F
Coil Voltage Rating	12 VDC
Contact Switching Load (Min)	100mA @ 5V
Contact Switching Voltage (Max)	30 VDC
Contact Voltage Rating	30 VDC

Body Features

Product Weight	9 g[.318 oz]
----------------	--------------

Contact Features

Contact Arrangement	1 Form A (NO)
Contact Current Class	5 – 10 A, 16 A
Contact Current Rating (Max)	10 A
Contact Material	AgCdO
Contact Number of Poles	1
Terminal Type	PCB-THT

Mechanical Attachment

Relay Mounting Type	Printed Circuit Board
---------------------	-----------------------

Dimensions

Length Class (Mechanical)	16 – 20 mm
Insulation Clearance Class	2.5 – 4 mm
Height Class (Mechanical)	14 – 15 mm
Insulation Clearance Between Contact & Coil	3.2 mm[.126 in]
Width Class (Mechanical)	10 – 12 mm
Product Width	10.2 mm[.4 in]
Product Length	18.2 mm[.717 in]
Product Height	14.7 mm[.579 in]

Usage Conditions

Environmental Ambient Temperature Class	70 – 85 °C
Environmental Ambient Temperature (Max)	85 °C[185 °F]

Packaging Features

Packaging Method	Bundle
------------------	--------

Product Compliance



For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Cadmium oxide (5.91% in Component Part) Article Safe Usage Statements: Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1393194-7
T77S1D10-05

TE Part # 1-1393194-6
T77S1D3-24



TE Part # 1-1393194-3
T77S1D3-05

TE Part # 1-1393194-5
T77S1D3-12



 TE Part # 1-1393194-8 T77V1D10-05	 TE Part # 2-1393194-1 T77V1D10-24	 TE Part # 1-1393194-0 T77S1D10-24	 TE Part # 1-1393194-9 T77V1D10-12
 TE Part # 1393194-6 T77S1D10-03	 TE Part # 1440005-1 T77V1D10-09	 TE Part # 2-1393194-0 T77V1D10-18	

Customers Also Bought

 TE Part #1-1721081-2 PCN 3A/5A SLIM PCB RELAY 3VDC	 TE Part #6609065-3 CORCOM EDP SERIES SINGLE PHASE FILTERS	 TE Part #1-1393589-8 C42334A 347A102=HS-STECKER	 TE Part #1393194-7 T77S1D10-05
 TE Part #1-2008552-2 CONNECTOR, INLINE VERT SCREWLESS	 TE Part #1-2176088-2 RP 1J 0.166W 976R 0.1% 25PPM 1K RL	 TE Part #1-1410297-2 MULTIGIG RT KEY/ESD .8" 45 DEG	 TE Part #103185-2 02 MODII HDR SRST B/A .100CL
 TE Part #1-1393194-9 T77V1D10-12	 TE Part #1-1825027-2 FSMRA4JHA04=R/A,TACT PB SW,260		

Documents



CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1393194-9_C7.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1393194-9_C7.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1393194-9_C7.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

T77 10 Amp Miniature PC Board Relay

English

OJ_OJE Series Relay Data Sheet English

English

Product Specifications

Definitions, Handling, Processing, Testing and Use of Relays

English

Product Environmental Compliance

Product Compliance

English

Product Compliance

English