

Agastat

TE Internal #: 2-1437471-4

Time Delay Relays, Knob, 240VAC Time Delay Relay Input Voltage, 10A@120VACA Time Delay Relay Contact Current Rating, On-Delay

View on TE.com >



Relays, Contactors & Switches > Relays > Time Delay Relays



Type of Control: Knob

Time Delay Relay Input Voltage: 240 VAC

Time Delay Relay Contact Current Rating: 10A@120VAC A

Mode of Operation: On-Delay

Delay Time: .1 – 10 minutes

Features

Product Type Features

Multiple Timing Ranges

Product Type	Relay	
Relay Type	Time Delay	
Product Category	Electromechanical Relays	
Magnetic Blow-Out Device	Without	
Configuration Features		

Electrical Characteristics		
Actuating System	AC	

Without

Time Delay Relay Input Voltage 240 VAC

Contact Features

Contact Arrangement	2 Form C, DPDT, 2 C/O
Type of Control	Knob
Time Delay Relay Contact Current Rating	10A@120VAC A
Delay Time	.1 – 10 minutes

Termination Features

Mechanical Attachment



Time Delay Relay Mounting Type	Socket
Dimensions	
Dimensions (L x W x H) (Approximate)	50 x 50 x 83 mm[1.97 x 1.97 x 3.27 in]
Usage Conditions	
Operating Temperature Range	-30 – 65 °C
Operation/Application	
Mode of Operation	On-Delay
Other	
Repeatability (Max)	±1% +4 msec

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2018 (181) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts





Customers Also Bought





BUDGET RING 12-10 5/8
















TE Part #1-796859-2 12POS TERMI-BLOK PLUG RT ANGLE







Documents

Product Drawings
SSC12BPA=240V 50 60HZ .1TO10SE

English

Datasheets & Catalog Pages 5-1773450-5_sec12_SSC

English