



Alcoswitch

TE Internal #: 2-1437597-7

Keylock Switches, Single Pole - Single Throw Configuration (Pole-Throw), Zinc Alloy, Remove Key Position 1, Hand Soldering Type

[View on TE.com >](#)

Relays, Contactors & Switches > Switches > Keylock Switches



Configuration (Pole-Throw): **Single Pole - Single Throw**

Cylinder Material: **Zinc Alloy**

Remove Key: **Position 1**

Soldering Type: **Hand**

Operating Function: **Position 1 Off, Position 2 (On)**

Features

Product Type Features

Product Type	Switch
Switch Type	Key Lock
Illuminated	No
Frame Material	Stainless Steel

Configuration Features

Configuration (Pole-Throw)	Single Pole - Single Throw
Operating Function	Position 1 Off, Position 2 (On)
Panel Cutout Size	19.3 x 16.3 mm [.76 x .64 in]
Number of Keylock Switch Positions	2

Electrical Characteristics

Contact Resistance	50 mΩ
Keylock Switch Voltage Rating	110 VAC, 120 VAC

Body Features

Actuator Travel	90°
Key Changes	25 Standard
Actuator Material	Brass

Contact Features

Contact Timing	Non-Shorting
----------------	--------------



Terminals/Fixed Contact Type	Screw/Solder
------------------------------	--------------

Keylock Switch Contact Current Rating	1 A
---------------------------------------	-----

Contact Finish	Silver
----------------	--------

Mechanical Attachment

Lock Body	Zinc Alloy
-----------	------------

Keylock Switch Mounting Type	Panel
------------------------------	-------

Housing Features

Cylinder Material	Zinc Alloy
-------------------	------------

Remove Key	Position 1
------------	------------

Usage Conditions

Oil-Tight	No
-----------	----

Other

Life Expectancy	10000 Cycles
-----------------	--------------

Comment	(On) indicates momentary position., All keylocks are supplied with 2 brass keys on a ring.
---------	--

Soldering Type	Hand
----------------	------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
------------------------------	---------------------------

EU ELV Directive 2000/53/EC	Compliant with Exemptions
-----------------------------	---------------------------

China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
---	--------------------------------------

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (.33% in Component Part)
--	--

Article Safe Usage Statements:
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2-1437597-3
2SWK132AL101=NON UL KEYLOCKS S



TE Part # 1-1437597-7
2SWK131AL101=NON UL KEYLOCK SW

Customers Also Bought



TE Part #1-747943-5
IDC D-Sub: Receptacle Kit, Wire to Wire, Signal, 2.74 mm



TE Part #2-1437597-3
2SWK132AL101=NON UL KEYLOCKS S



TE Part #1437597-7
2SKF132AEL01=NON UL KEYLOCK S



TE Part #2-1393117-4
KUP-11A25-120=KU



TE Part #112263-90
DEUTSCH HD30 MOUNTING HARDWARE



TE Part #YDTS24W21-11PNV001
Jam Nut: D38999, 21-11 Insert



TE Part #185636-1
PROTECT CAP 2.5MM PLUG



TE Part #103959-1
10X2 MTE RCPT SR LATCH .100CL



Documents

CAD Files

[3D PDF](#)

[3D](#)

Customer View Model

[ENG_CVM_CVM_2-1437597-7_99.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-1437597-7_99.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-1437597-7_99.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Alcoswitch Products](#)

English