

2-160971-1 ✓ ACTIVE

AMP-TY


TE Internal #: 2-160971-1

Cable Ties, Standard, Bag, 130Newton Tensile Strength, 29.2lbf Tensile Strength, Cable Tie Length 140 mm [5.5 in], Cable Tie Width .141 in [3.6 mm]

[View on TE.com >](#)



Wire & Cable > Wire & Cable Accessories > Cable Ties



Cable Tie Style: **Standard**

Cable Tie Packaging Method: **Bag**

Tensile Strength: **29.2 lbf**

Cable Tie Length: **140 mm [ 5.5 in ]**

## Features

### Product Type Features

Product Type	Cable Tie
Cable Tie Style	Standard
Tensile Strength	29.2 lbf

### Body Features

Cable Tie Color	Natural
Cable Tie Material	Polyamide 6.6 GF

### Dimensions

Bundle Range Diameter	35 mm[1.37 in]
Cable Tie Length	140 mm[5.5 in]
Cable Tie Width	3.6 mm[.141 in]
Cable Tie Thickness	1.12 mm[.044 in]

### Packaging Features

Cable Tie Packaging Method	Bag
Cable Tie Packaging Quantity	100

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)









EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant


China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2016 (169) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


## Compatible Parts

 <p>TE Part # CAT-T3437-C6298 CM-SCE-TP MILITARY GRADE MARKERS</p>	 <p>TE Part # CAT-T3437-K1 K-TYPE TIE-ON MARKERS</p>	 <p>TE Part # CAT-T3437-H85999 HTCM-SCE-TP HIGH TEMPERATURE MARKERS</p>	 <p>TE Part # EC6518-000 13611808</p>
 <p>TE Part # EC6496-000 13611442</p>	 <p>TE Part # EC6513-000 13611707</p>	 <p>TE Part # EC6409-000 13611202</p>	 <p>TE Part # EC6453-000 13611303</p>



### Customers Also Bought





## Documents

### Product Drawings

[CABLE TY 140X3.6 NAT](#)

English

---

### Datasheets & Catalog Pages

[Connectivity Solutions for Industrial Applications](#)

English

[CABLE TIES](#)

English