

2-160996-2 ✓ ACTIVE

AMP-TY


TE Internal #: 2-160996-2

Cable Ties, Standard, Bag, 130Newton Tensile Strength, 29.2lbf Tensile Strength, Cable Tie Length 200 mm [7.9 in], Cable Tie Width .141 in [3.6 mm]

[View on TE.com >](#)



Wire & Cable > Wire & Cable Accessories > Cable Ties



Cable Tie Style: **Standard**

Cable Tie Packaging Method: **Bag**

Tensile Strength: **29.2 lbf**

Cable Tie Length: **200 mm [ 7.9 in ]**

## Features

### Product Type Features

Product Type	Cable Tie
Cable Tie Style	Standard
Tensile Strength	29.2 lbf

### Body Features

Cable Tie Color	Black
Cable Tie Material	Polyamide 6.6 GF

### Dimensions

Bundle Range Diameter	2 – 50 mm [.078 – 1.97 in]
Cable Tie Length	200 mm [7.9 in]
Cable Tie Width	3.6 mm [.141 in]
Cable Tie Thickness	1.2 mm [.047 in]

### Packaging Features

Cable Tie Packaging Method	Bag
Cable Tie Packaging Quantity	100

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant




China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



TE Part # 2-160967-1  
CABLE TY 98X2.5 NAT


### Customers Also Bought



TE Part #2-1623730-1  
Wirewound Resistor: Vertical Mount




TE Part #2-1623789-7  
Wirewound Resistor: Vertical Mount



TE Part #282858-8  
8P. TERMI-BLOK PCB MOUNT 90



TE Part #4-2176371-5  
RQ 0603 13K3 0.1% 10PPM 5K RL



## Documents

### Product Drawings

[CABLE TY 200X3.6 BLA](#)

English

### Datasheets & Catalog Pages

[CABLE TIES](#)

English