

W57-XB7A4A10-15 ✓ ACTIVE

Potter & Brumfield W57

TE Internal #: 1423675-9

Potter & Brumfield W57, Circuit Breakers, Thermal, Series Trip, White with Red Rate Marking (Vertical) Button Color, 250VAC Voltage Rating AC

[View on TE.com >](#)



Relays, Contactors & Switches > Circuit Breakers



Circuit Breaker Type: **Thermal**

Circuit Function: **Series Trip**

Illuminated: **No**

Button Color: **White with Red Rate Marking (Vertical)**

Voltage Rating AC: **250 VAC**

Features

Product Type Features

| | |
|----------------------|-----------------|
| Illumination Type | No Light |
| Product Type | Circuit Breaker |
| Actuator Type | Push to Reset |
| Circuit Breaker Type | Thermal |
| Illuminated | No |

Configuration Features

| | |
|------------------|---------------|
| | .48 x .433 in |
| Earthing Switch | Without |
| Circuit Function | Series Trip |

Electrical Characteristics

| | |
|--------------------------------|----------------------|
| Voltage Rating AC | 250 VAC |
| Voltage Rating DC | 50 VDC |
| Circuit Breaker Current Rating | 15 A |
| Interrupt Capacity | 1000A @ 250VAC/50VDC |

Body Features

| | |
|--------------|--|
| Button Color | White with Red Rate Marking (Vertical) |
|--------------|--|

Contact Features

| | |
|--------------------|---|
| Pole Configuration | 1 |
|--------------------|---|



Trip Time at 200% 4 – 40 seconds

Termination Features

Circuit Breaker Termination Type 6.35 [.25] Straight Quick Connect Tab

Mechanical Attachment

Mounting Hardware Packaging Assembled to Bushing

Mounting Options Knurled Nut/Hex Nut

Mounting Bushing 10.8 x 12.6mm Long, Metal

Circuit Breaker Mounting Type Panel Mount

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU Compliant with Exemptions

EU ELV Directive 2000/53/EC Not Compliant

China RoHS 2 Directive MIIT Order No 32, 2016 Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006
 Current ECHA Candidate List: JAN 2021 (211)
 Candidate List Declared Against: JAN 2021 (211)
 SVHC > Threshold:
 Cadmium oxide (7.95% in Contact)
Article Safe Usage Statements:
 Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.


Halogen Content Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | Potter & Brumfield W57



Customers Also Bought





Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1423675-9_C.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1423675-9_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1423675-9_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[W57 Compact Push To Reset Only Thermal Circuit Breaker](#)

English

[Industrial Relays Quick Reference Guide](#)

English

[Industrial Relays Quick Reference Guide](#)

Japanese

[Industrial Relays Quick Reference Guide](#)