

1596970-1 ✓ ACTIVE

AMP

TE Internal #: 1596970-1

Portable Crimp Tools, Commercial Crimp Tooling, Not Releasable,
Not Adjustable, Removable/Interchangeable, TE Product
Specification (114-), Manual

[View on TE.com >](#)



Application Tooling > Portable Crimp Tools



Tool Grade: **Commercial Crimp Tooling**

Ratchet Configuration: **Not Releasable, Not Adjustable**

Die Sets Type: **Removable/Interchangeable**

Specification Type: **TE Product Specification (114-)**

Power Technology Type: **Manual**

Features

Other

Tool Grade	Commercial Crimp Tooling
Ratchet Configuration	Not Releasable, Not Adjustable
Die Sets Type	Removable/Interchangeable
Specification Type	TE Product Specification (114-)
Power Technology Type	Manual
Tooling Type	PRO-CRIMPER Hand Tool

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1596981-1
DIE SET ASSY

Customers Also Bought



TE Part #1375820-2
Receptacle Housing: 2.54mm, 1 Row, CST-100 II



TE Part #179228-2
AMP COMMON TERMINATION HOUSINGS



TE Part #179227-1
AMP COMMON TERMINATION CONTACTS




TE Part #172162-1
12 CIR UNIV M-N-L CAP



TE Part #1375819-2
CST-100 II CONTACT 15 GOLD PLT



TE Part #1375819-1
CST-100 II CONTACT TIN PLT



TE Part #1-282841-1
TERMI-BLOK PCB MOUNT 11P.5



TE Part #1-2329389-1
PB OFF/ON FC YLW M1 TERM WHI LED IP68 50



Documents

Product Drawings

[SHELL BARREL CRIMP TOOL](#)

Japanese

Datasheets & Catalog Pages

[1-1773865-2_1015_Commercial Manual Hand Tools](#)

English

Bottoming Dies

English

Product Specifications

[SHELL BARREL CRIMP TOOL](#)

Japanese

[SHELL BARREL CRIMP TOOL](#)

Japanese