



Cable Assemblies > Copper Cable Assemblies > Power Cable Assemblies



Power Cable Assembly Configuration: **Double-Ended**
Power Cable Assembly Shielded: **No**
Cable Assembly Length: **.25 m**
Power Cable Assembly Color: **Black**
Operating Temperature Range: **-25 – 125 °C [-13 – 257 °F]**

Features

Product Type Features

Product Type	Cable Assembly
Cable Assembly Category	Power
Power Cable Assembly Shielded	No
Power Cable Assembly Type	Power
Power Cable Assembly Connector Type (End A)	Power Connector
Power Cable Assembly Connector Type (End B)	Power Connector

Configuration Features

Number of Positions	3
Power Cable Assembly Configuration	Double-Ended

Body Features

Power Cable Assembly Color	Black
----------------------------	-------

Housing Features

Power Cable Assembly Housing Material	Thermoplastic
Power Cable Assembly Housing Color	Black

Dimensions

Wire Size	12 AWG
-----------	--------

Usage Conditions



Operating Temperature Range	-25 – 125 °C[-13 – 257 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-0
UL Rating	Listed

Other

Cable Assembly Length	.25 m
-----------------------	-------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2204535-2
ELCON MINI 2X3P STACKED RA HDR,
SDR, LUBR

Also in the Series | ELCON Mini

Insertion & Extraction Tools(1)

Power Cable Assemblies(6)

Rectangular Power Connectors(32)

Customers Also Bought

TE Part #176285-1
AMP UNIVERSAL POWER CAP 6P

TE Part #176273-1
AMP UNIVERSAL POWR PLUG 4P

TE Part #175150-2
AMP UNIVE. POWER CONN TAB
CONT

TE Part #176274-1
AMP UNIVERSAL POWER PLUG 6P

TE Part #176294-1
UNIV POWER CAP HSG 4P P/MOUNT

TE Part #M902-2244
DEUTSCH HDP20 BACKSHELLS

TE Part #174463-1
MULTILOCK, CONNECTOR HOUSING

TE Part #147432-2
29/30 MODII HDR DRRA SHRD .100CL

TE Part #1-963746-1
SPECIAL TERMINAL 17-13 AWG PTPB
LP

TE Part #1SNA008370R2200
BDA 1000



Documents

Product Drawings

CA,ET, 3POS, LONG PULL-TAB,NO DETECT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2304886-1_2.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2304886-1_2.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2304886-1_2.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

ELCON Mini Power Interconnects QRG (English)

English