

HT-SCE-3/32-2.0-S1-9

✓ ACTIVE

TE Internal #: 2355930001

Printable Tubing, Ladder Printable Tubing Type, High Temperature Printable Tubing Grade, 2:1 Printable Tubing Shrink Ratio, White, 1 Prescore

[View on TE.com >](#)



Identification & Labeling > Printable Tubing > HT-SCE HIGH TEMPERATURE SLEEVES



Printable Tubing Type: **Ladder**

Printable Tubing Grade: **High Temperature**

Printable Tubing Shrink Ratio: **2:1**

Primary Product Color: **White**

Number of Prescores: **1**

[All HT-SCE High Temperature Sleeves \(55\)](#)

Features

Product Type Features

Printable Tubing Type	Ladder
Printable Tubing Grade	High Temperature

Body Features

Printable Tubing Shrink Ratio	2:1
Primary Product Color	White
Markers per Sleeve	2

Dimensions

Product Length	25 mm[1 in]
Supplied Inner Diameter	2.4 mm[.093 in]
Recovered Inside Diameter	.7 mm[.031 in]
Compatible Cable Diameter Range	.8 – 1.9 mm[.032 – .075 in]

Usage Conditions

Operating Temperature Range	-55 – 225 °C[-67 – 437 °F]
-----------------------------	----------------------------

Operation/Application

Recommended Ribbon	See TE Document 411-121005 the Printer Product Ribbon Matrix
--------------------	--



Printer/Label Features

Recommended Printer	See TE Document 411-121005 the Printer Product Ribbon Matrix
Printer Technology	Thermal Transfer
Number of Prescores	1

Packaging Features

Packaging Quantity	250
--------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2186500-1
T3212-PRINTER

TE Part # 1-2186502-1
T3224-PRINTER

TE Part # 1-2186503-1
T3224-SWARE-PRINTER

TE Part # CP8122-000
T6112DS-PRINTER

TE Part # 754073-000
TMS-RJS-RIBBON-4HT

TE Part # 1-2186501-1
T3212-SWARE-PRINTER

Customers Also Bought

TE Part #EC9896-000
ZHD-SCE LFH & FLUID RESISTANT SLEEVES

TE Part #1958311-1
TERMINAL,SOLIS R 3/0 10.75mm

TE Part #3-641240-7
Nylon Gold Plated Receptacle: 2.54 mm, No Mating Alignment, MTA 100

TE Part #467122-000
Heat Shrink Boots: Poly Mold, Lipped

TE Part #3-1123723-1
3.96 EP HDR ASSY 11P(BLUE)

TE Part #6-103945-0
2X11 MTE SHRD PIN SR LTCH .100

TE Part #7-102393-3
50 AMPMODU MT ASSY DR.100CL SN

TE Part #234471-000
STXR40AC00-1210AI

TE Part #522827-000
STXR54AB00-0805AI

Documents



Product Drawings

HT-SCE-3/32-2.0-S1-9

English

Datasheets & Catalog Pages

HT-SCE Heat Shrinkable Sleeves

English

IDENTIFICATION SELECTION GUIDE

English

Product Specifications

Product Specification

English

Instruction Sheets

Instruction Sheet (non U.S.)

English