



Wire & Cable > Wire & Cable Accessories > Cable Ties



Cable Tie Style: **Standard**
Cable Tie Packaging Method: **Bag**
Tensile Strength: **50 lbf**
Cable Tie Length: **202 mm [8 in]**

Features

Product Type Features

Product Type	Cable Tie
Cable Tie Style	Standard
Tensile Strength	50 lbf

Body Features

Cable Tie Color	Natural
Cable Tie Material	Nylon

Dimensions

Bundle Range Diameter	44.45 mm[1.75 in]
Cable Tie Length	202 mm[8 in]
Cable Tie Width	4.6 mm[.181 in]
Cable Tie Thickness	1.19 mm[.047 in]

Industry Standards

Agency/Standard	UL
-----------------	----

Packaging Features

Cable Tie Packaging Method	Bag
Cable Tie Packaging Quantity	100

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought



TE Part #1-745491-6
IDC D-Sub: Receptacle Assembly,
Wire to Wire, Signal, 2.74 mm

TE Part #1775470-8
AMP HPI 2.0MM HEADERS

TE Part #1487594-2
USB, A-B, 28/28, BLACK, 0.25M

TE Part #1-604771-9
CABLE TIE, 4" L, NATURAL, 100PK

TE Part #1-603227-9
CABLE TIE, NAT, 6" L, 100/PACK

TE Part #1825138-1
A201KAB04

TE Part #2-320882-1
PIDG RING TONGUE TERMINALS

TE Part #YDTS20W15-05PNV001
D38999: Square Flange, 15-05 insert

TE Part #2-520184-2
ULTRAFast 250 ASSY REC 22-18
TPBR LP

TE Part #1487594-3
USB, A-B, 28/28, BLACK, 0.16M

Documents

Product Drawings

CABLE TIE, 8" L, NATURAL, 100PK

English

Datasheets & Catalog Pages

CABLE TIES

English