




Terminals & Splices > Ring Terminals & Spade Terminals



Terminal & Splice Type: **Ring Tongue**

Wire Size: **28280 CMA**

Ring & Spade Stud Size: **#10, M5**

Features

Product Type Features

Ring & Spade Stud Size	#10, M5
Ring & Spade Barrel Type	Closed Barrel
Sealable	Yes
Insulated	No
Ring & Spade Wire/Cable Type	Aluminum, Copper
Support Style	Insulation Support

Configuration Features

Number of Holes	1
Terminal Angle	Straight

Electrical Characteristics

Voltage (Max)	600 V
---------------	-------

Body Features

Weight per Piece	16.8 g
Ring & Spade Plating Material	Tin

Contact Features

Terminal & Splice Type	Ring Tongue
Ring & Spade Terminal Orientation	Straight
Underplating Material	Nickel

Dimensions

--	--



Wire Size	28280 CMA
Stud Diameter	5 mm[.197 in]
Tongue Thickness	2.26 mm[.089 in]
Ring & Spade Overall Length	48.26 mm[1.89 in]
Barrel Inside Diameter	7.11 mm[.28 in]
Ring & Spade Wire Insulation Diameter (Max)	6.35 mm[.25 in]
Ring & Spade Wire Insulation Diameter	5.72 – 6.35 mm[.225 – .25 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-55 – 150 °C[-67 – 302 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	25
Ring & Spade Packaging Method	Box

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1490556-1
HYP10 COPALUM SEALED 6AWG DIE SET

TE Part # 68007
HYP8/10 COPALUM SEALED 6AWG DIE SET

Customers Also Bought

TE Part #1617122-7
JMACD-18XM = M39016/15-080M

TE Part #1617003-2
B07B311BC3 = 07 10AMP RELAY

TE Part #1617087-7
CEW-1C-24A = HALF 10A.1POLE.SI

TE Part #531134-7
3ROW BOX REC 210P 100CL UNSEAL

TE Part #218344-002
55A0813-20-9

TE Part #366439-000
55A1811-4-9-9

TE Part #476095-000
55A4121-20-6/9-9

TE Part #726006-000
55PC1821-20-6/9-9-F871



Documents

Product Drawings

TERMINAL,COPALUM R 6 10

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_277148-1_H.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_277148-1_H.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_277148-1_H.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

COPALUM Lite Sealed Terminals and Splices

English

Product Specifications

Application Specification

English