



Wire Protection & Management > Heat Shrink Molded Shapes > Wire End Caps



End Cap Wall Type: **Single**

Material Code: **25**

Sealant: **None**

End Cap Material Systems Code: **25**

Adhesive Pre-Coat: **No**

Features

Product Type Features

Size Code	62
End Cap Wall Type	Single

Body Features

Color	Black
Material	Crosslinked Polyolefin
Shrink Ratio	2:1
Pliancy	Flexible
Material Code	25
Sealant	None
End Cap Material Systems Code	25
Adhesive Pre-Coat	No

Dimensions

Length	68 mm[2.7 in]
Recovered Inside Diameter (Max)	11.4 mm[.45 in]
Recovered Wall Thickness (Nominal)	2.29 mm[.09 in]
Expanded Inside Diameter (Min)	25.4 mm[1 in]
Wall Thickness	Medium

Usage Conditions

Flammability	Flame-Retardant
--------------	-----------------



Resistance Protection	Suitable for long term fluid exposure at elevated temperatures
Resistance Properties	Immersion Protection
Operating Temperature Range	-75 – 150 °C[-103 – 302 °F]

Industry Standards

Government Qualified	No
----------------------	----

Other

Molded Part Shape Code	101A
End Cap Adhesive Type	Adhesive Purchased Separately

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # 657863-000
[S1125-KIT-8](#)




TE Part # CJ2087-000
[HL2010E-KIT-120V](#)


Customers Also Bought




TE Part #3-1625931-1
[MCU 10K 10% 1" PL](#)




TE Part #1-640510-0
[06P MR II CAP HSG V0 RED](#)



TE Part #244520-000
[Bulbous Heat Shrink Boots: Lipped, Straight](#)




TE Part #465411-000
[55FB1531-22-7L/7L3/7L6-0](#)




TE Part #1824133001
[55K9082-24-2/6](#)



TE Part #491960-000
[55A1131-28-0/2/9-9](#)



TE Part #353757-000
[55A1141-22-0/2/4/9-9](#)



TE Part #205933-000
[55FB1521-22-7L/7L6-0](#)



TE Part #ZPF000000000167407
[983-6RS 10-05 SY](#)

Documents

Product Drawings

[101A062-25-0](#)

English

Datasheets & Catalog Pages

[1654025_Sec4_-25](#)

English

[1654025_Sec4_101A011to094](#)

English



Raychem Molded Parts Visual Guide

English

Product Environmental Compliance

Safety Datasheet

Safety Datasheet

German

Safety Datasheet

English

Safety Datasheet

Safety Datasheet

French

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet