
OEG | OEG Miniature PCB Relay PCH

TE Internal #: 1721767-5 OEG Miniature PCB Relay PCH, Power Relays, Standard, Monostable, DC, 300 – 400mW Coil Power Rating Class, 400mW Coil Power Rating DC

View on TE.com >

Relays, Contactors & Switches > Relays > Power Relays > PCFN SOLAR RELAY



Power Relay Type: Standard

Coil Magnetic System: Monostable, DC

Coil Power Rating Class: 300 – 400 mW

Coil Power Rating DC: 400 mW

Coil Resistance: 360 Ω

All PCFN SOLAR RELAY (33)

TE

Features

Product Type Features

Power Relay Type	Standard					
Electrical Characteristics						
Insulation Initial Dielectric Between Coil & Contact Class	3500 – 4000 V					
Insulation Initial Dielectric Between Open Contacts	750 Vrms					
Contact Limiting Making Current	5 A					
Contact Limiting Short-Time Current	5 A					
Contact Limiting Continuous Current	5 A					
Insulation Creepage Class	3 – 5.5 mm					
Insulation Initial Dielectric Between Contacts & Coil	4000 Vrms					
Contact Limiting Breaking Current	5 A					
Coil Magnetic System	Monostable, DC					
Coil Power Rating Class	300 – 400 mW					
Coil Power Rating DC	400 mW					

C For support call+1 800 522 6752

OEG Miniature PCB Relay PCH, Power Relays, Standard, Monostable, DC, 300 – 400mW Coil Power Rating Class, 400mW Coil Power Rating DC



Coil Resistance	360 Ω				
Coil Special Features	UL Coil Insulation Class F				
Coil Voltage Rating	12 VDC				
Contact Switching Load (Min)	100mA @ 5V				
Contact Switching Voltage (Max)	30 VDC				
Contact Voltage Rating	30 VDC				
Body Features					
Insulation Special Features	Tracking Index of Relay Base PTI250				
Product Weight	7 g[.247 oz]				
Contact Features					
Contact Arrangement	1 Form A (NO)				
Contact Current Class	2 – 5 A, 16 A				
Contact Current Rating (Max)	5 A				
Contact Material	AgSnO				
Contact Number of Poles	1				
Terminal Type	PCB-THT				

Mechanical Attachment

Relay Mounting Type	Printed Circuit Board			
Dimensions				
Length Class (Mechanical)	16 – 20 mm			
Insulation Clearance Class	0 – 2.5 mm			
Height Class (Mechanical)	15 – 16 mm			
Width Class (Mechanical)	8 – 10 mm			
Product Width	10 mm[.394 in]			
Product Length	20 mm[.787 in]			
Product Height	15.2 mm[.598 in]			
Usage Conditions				
Environmental Ambient Temperature Class	50 – 70 °C			
Environmental Ambient Temperature (Max)	85 °C[185 °F]			
Packaging Features				
Packaging Method	Bundle			

OEG Miniature PCB Relay PCH, Power Relays, Standard, Monostable, DC, 300 -400mW Coil Power Rating Class, 400mW Coil Power Rating DC



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant	
EU ELV Directive 2000/53/EC	Compliant	
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold	
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC	
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.	
Solder Process Capability	Wave solder capable to 265°C	

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-onreach


Compatible Parts




Also in the Series OEG Miniature PCB Relay PCH

OEG Miniature PCB Relay PCH, Power Relays, Standard, Monostable, DC, 300 – 400mW Coil Power Rating Class, 400mW Coil Power Rating DC





Customers Also Bought



Free Height Receptacle Conn: Board- Board, Vertical, 40, 0.8mm	PCFN SOLAR RELAY	RT33L048	IMP100S,H,RA2P10C,LG,OI
ETE			
TE Part #5-1393238-7 RTD14F03	TE Part #6-2176367-8 RQ 0603 23K2 0.1% 10PPM 1K RL		

Documents

Product Drawings PCH-112D2M-WG

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1721767-5_C1.2d_dxf.zip

OEG Miniature PCB Relay PCH, Power Relays, Standard, Monostable, DC, 300 – 400mW Coil Power Rating Class, 400mW Coil Power Rating DC



English

Customer View Model ENG_CVM_CVM_1721767-5_C1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1721767-5_C1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Datasheets & Catalog Pages PCH Series Relay Data Sheet - English

English

Product Specifications Definitions, Handling, Processing, Testing and Use of Relays

English