



Identification & Labeling > Printable Tubing



Printable Tubing Type: **Ladder**
Printable Tubing Grade: **Military**
Printable Tubing Shrink Ratio: **3:1**
Primary Product Color: **Black**
Markers per Sleeve: **1**

Features

Product Type Features

Printable Tubing Type	Ladder
Printable Tubing Grade	Military

Body Features

Printable Tubing Shrink Ratio	3:1
Primary Product Color	Black
Markers per Sleeve	1

Dimensions

Product Length	12.7 mm[.5 in]
Supplied Inner Diameter	4.75 mm[.87 in]
Recovered Inside Diameter	1.57 mm[.062 in]
Compatible Cable Diameter Range	1.75 – 4.06 mm[.069 – .16 in]

Usage Conditions

Operating Temperature Range	-55 – 135 °C[-67 – 275 °F]
-----------------------------	----------------------------

Operation/Application

Recommended Ribbon	See TE Document 411-121005 the Printer Product Ribbon Matrix
--------------------	--

Printer/Label Features

Recommended Printer	See TE Document 411-121005 the Printer Product Ribbon Matrix
---------------------	--



Printer Technology

Thermal Transfer

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-2186500-1 T3212-PRINTER	 TE Part # 1-2186502-1 T3224-PRINTER	 TE Part # 1-2186503-1 T3224-SWARE-PRINTER	 TE Part # CP8122-000 T6112DS-PRINTER
--	--	--	---



TE Part # 1-2186501-1
T3212-SWARE-PRINTER

Also in the Series | TMS-SCE



Printable Tubing(142)


Customers Also Bought



TE Part #2102735-1
BP, Half Left End, MULTIGIG RT 2R



TE Part #1-1469492-1
MULTIGIG RT 9MM GUIDE/ESD 0 DEG



TE Part #2102736-1
BP, Center, MULTIGIG RT 2R




TE Part #2102737-1
BP, Right End, MULTIGIG RT 2R



TE Part #1-1469492-7
MULTIGIG RT 9MM GUIDE/ESD 270 DEG



TE Part #164581-000
B-106-1403



TE Part #027099-000
342A048-25/225-0



TE Part #172921-000
TXR54AB00-1607AI



TE Part #2102771-1
DC, 7Row, Center, MULTIGIG RT 2R



TE Part #YCFX26W1108PZN0000
PLUG ASSY



Documents

Product Drawings

TMS-SCE-1K-3/16-2.0-0

English

Instruction Sheets

Instruction Sheet (non U.S.)

English