

816-AG10D × OBSOLETE


DIPLOMATE 800 Series

TE Internal #: 3-1437537-7

TE Internal Description: 816-AG10D=SOCKET ASSY

DIP Socket: Standard, Screw Machine, Open, Gold

[View on TE.com >](#)



All DIP Socket: Standard, Screw Machine, Open, Gold (1)

Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2020 (205) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | [DIPLOMATE 800 Series](#)




DIP Sockets(5)

Customers Also Bought



TE Part #1-5499374-0
AMP-LATCH UNIVERSAL HEADERS



TE Part #1419111-2
20C217=SPRING,HOLD-DOWN,KH,.03



TE Part #102387-6
26 MODIV HSG COMP DR .100 POL



TE Part #1393143-8
27E125=SOCKET,R10,10,SLG,PHE



TE Part #1-103309-0
050 LOPRO HDR SP 30DP



TE Part #103309-6
026 LOPRO HDR SP 30DP



TE Part #1419106-1
27E006=SOCKET,KH,14,SLG,G/T,PH



TE Part #87232-8
08 MODII HDR SRRA UNSHRD .100



TE Part #103240-3
06 MODII HDR DRST B/A .100CL



TE Part #1-1437539-4
DIP Socket: Standard, Stamped &
Formed, Open, Gold

Documents

Product Drawings

816-AG10D=SOCKET ASSY

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-1437537-7_E.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_3-1437537-7_E.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-1437537-7_E.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[DIP Sockets Quick Reference Guide \(EN\)](#)

English