



Relays, Contactors & Switches > Switches > Rocker Switches



Rocker Switch Type: **Power**
Rocker Switch Mounting Type: **Panel**
Indicator/Imprint Legend: **None**
Switch Contact Plating Material: **Silver**
Lamp: **Without**

Features

Product Type Features

Product Type	Switch
Rocker Switch Type	Power
Lamp	Without
Rocker Switch LED	Without
Actuator Type	Beveled Frame, Snap-In
Actuator Style	Paddle

Configuration Features

Indicator/Imprint Legend	None
Configuration (Pole-Throw)	Double Pole - Double Throw
Operating Function	(On) Off (On)

Electrical Characteristics

Rocker Switch Voltage Rating	125 VAC
------------------------------	---------

Body Features

Body Color	Black
------------	-------



Actuator Color	Black
----------------	-------

Contact Features

Switch Contact Plating Material	Silver
Rocker Switch Contact Current Rating	5 A

Termination Features

Termination Type	Wire Lugs
------------------	-----------

Mechanical Attachment

Mounting Angle	Vertical
Rocker Switch Mounting Type	Panel

Housing Features

Process Sealed	No
----------------	----

Industry Standards

VDE Tested	No
------------	----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (4% in Component) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part




numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-1571986-1
A101J1AV2Q004=SGL POLE,ROCKER



TE Part # 1571986-8
A101J1AQ004=SGL POLE,ROCKER



TE Part # 1571986-7
A101J1AB004=SGL POLE,ROCKER




TE Part # 3-1571987-8
A207J61ZQ0004=DBL POLE,ROCKER



TE Part # 7-1571986-2
A101J1AV2Q004AM marking O -

Also in the Series | Alcoswitch Gemini A Series



Rocker Switches(6)



Toggle Switches(38)

Customers Also Bought



TE Part #1-1775441-0
AMP HPI 1.5MM RECEPTACLE HOUSINGS



TE Part #1-2176328-6
CRGP 1206 180R 1%



TE Part #1622583-1
LR1 1% 8K2



TE Part #1622595-1
LR1 1% 9K1





TE Part #1011-230-0205
DEUTSCH DT BACKSHELLS



TE Part #1461373-9
STD OEG Miniature PCB OJT Power Relays



TE Part #CV21104001
RW-175-E-1/4-X-SP



TE Part #1423675-9
W57-XB7A4A10-15=CKTBKR,THERM,P



TE Part #1-1478912-0
SMA R/A PLG S/CLMP RG174 GSS



TE Part #1-929939-1
TIMER, RECEPTACLE AND TAB

Documents

Product Drawings
A205J61ZQ0004=DBL POLE,ROCKER

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-1571987-4_A_c-3-1571987-4-a.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-1571987-4_A_c-3-1571987-4-a.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-1571987-4_A_c-3-1571987-4-a.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages
GEMINI_SERIES_SWITCHES_QUICK_REF_GUIDE_2-1773458-5

English